

MARINE PUSH PULL SWITCHES



M-606



M-626

Description

Littelfuse Push Pull Switches are designed for universal applications within harsh environments. Their mounting, body, and actuator features are designed for ease-of-use and extended product lifecycle.

With heavy duty brass bodies, the Marine Push Pull Switches are designed for circuit control within the Marine environment.

Web Resources

Download 2D print and technical resources at:
littelfuse.com/MarinePushPull

Specifications

Circuitry:	Single Pole, Single Throw - Normally Open
Housing:	Brass
Ingress Protection:	Hencol Coated (where applicable)

Applications

- Construction Equipment
- Agricultural Equipment
- Material Handling Equipment
- Commercial Vehicles
- Marine Vehicles

Ordering Information

PART NUMBERS			DESCRIPTION	MOUNTING	VOLTAGE RATING	INGRESS PROTECTION	ACTUATOR	POSITIONS	TERMINATION
BULK	BOX	RETAIL							
M-482	—	—	Normally Open Push Pull Switch	Face Nut through 0.375 (9.525mm)-32 Panel Hole	10A at 12V DC	—	Plated Brass Knob	2: Off - On	2 Screws
M-531	—	M-531-BP	Marine Light Switch	Face Nut through 0.375 (9.525mm)-32 Panel Hole	10A at 12V DC	—	Plated Brass Knob	3: Off - On (1) - On (2)	3 Screws
M-532	—	—	Marine Light Switch	Face Nut through 0.375 (9.525mm)-32 Panel Hole	10A at 12V DC	—	Plated Brass Knob	3: Off - On (1&2) - On (1&3)	4 Screws
M-606	M-606-BX	M-606-BP	Normally Open Push Pull Switch	Face Nut through 0.375 (9.525mm)-32 Panel Hole	10A at 12V DC	Hencol Coated	Plated Brass Knob	2: Off - On	2 stripped 18AWG leads
M-608	M-608-BX	M-608-BP	Normally Open Push Button Switch	Face Nut through 0.625 (15.8753mm)-32 Panel Hole	10A at 12V DC	Hencol Coated	Black Rubber Boot with "Push" Imprint	2: Off - (On)	2 stripped 18AWG leads
M-626	M-626-BX	M-626-BP	Normally Open Push Button Starter Switch	Face Nut through 0.625 (15.8753mm)-32 Panel Hole	35A at 12V DC	—	Black Rubber Boot with "Push" Imprint	2: Off - (On)	2 Screws
M-626-02	—	—	Normally Open Push Button Starter Switch	Face Nut through 0.625 (15.8753mm)-32 Panel Hole	35A at 12V DC, 20A at 24V DC	—	Black Rubber Boot with "Push" Imprint	2: Off - (On)	2 Screws
M-628	—	M-628-BP	Normally Open Push Pull Switch	Face Nut through 0.375 (9.525mm)-32 Panel Hole	10A at 12V DC	—	Plated Brass Knob	2: Off - On	2 Screws
M-639	—	—	Normally Closed Push Button Switch	Face Nut through 0.625 (15.8753mm)-32 Panel Hole	10A at 12V DC	—	Plated Brass Plunger	2: On - (Off)	2 Screws
M-639-01	—	—	Normally Closed Push Button Switch	Face Nut through 0.625 (15.8753mm)-32 Panel Hole	10A at 12V DC	—	Plated Brass Plunger	2: On - (Off)	2 Blades