


# LF11215TMR Series

## TMR Bipolar Switch 17 Gauss 1.5uA Push Pull Sensor


RoHS



Functional Block Diagram



TMR Switch Typical Applications Circuit



**Note:** It is strongly recommended that an external bypass capacitor be connected in-close-proximity to the device between the supply and ground pins to reduce noise. The recommended value for the external bypass capacitor is 0.1µF.

### Description

The LF11215TMR TMR Switch is a digital bipolar magnetic switch that integrates TMR and CMOS technology in order to provide a magnetically triggered digital switch with high sensitivity, high speed, and low power consumption.

It contains a TMR magnetic sensor and CMOS signal processing circuitry within the same package, including an on-chip TMR voltage generator for precise magnetic sensing, a TMR voltage amplifier and comparator plus a Schmitt trigger to provide switching hysteresis for noise rejection, CMOS push-pull output and X axis sensing direction.

An internal band gap regulator is used to provide a temperature compensated supply voltage for internal circuits, permitting a wide range of supply voltages. It draws only 1.5uA (see Features below) resulting in low power operation, additionally it has fast response, accurate switching points, excellent thermal stability, and immunity to stray field interference. It is available in the SOT23-3 package. The output of the LF11215TMR switches low (turns on) when the magnetic field parallel to the sensing axis exceeds the operate point threshold, BOP. When the magnetic field is reduced below the release point BRP device output switches high (turns off). The difference between the BOP and the BRP is the hysteresis BH of the device

### Features and Benefits

- Tunneling Magnetoresistance (TMR) Technology
- Low power consumption at 1.5uA
- X axis sensing direction
- High Frequency up to 1000Hz
- Operation with North and South Pole
- 1.8V to 5.5V Operating Range
- High Tolerance to External MagneticField Interference
- Low Switching Points for HighSensitivity
- Excellent Thermal Stability

### Applications

- Proximity Switches
- Utility Meters including Gas, Waterand Heat Meters
- Speed Sensing
- Low power applications
- Rotary and Linear Position sensing

### Output Behavior Versus Magnetic Pole

Parameter	Test Conditions	Output (volts)
South Pole	$B > B_{OPS}$	Low (On)
North Pole	$0 < B < B_{RPS}$	High (Off)

**Note:**

The output is "High" when power is turned on under zero magnetic field. When a S Pole approaches the pin 1 side,  $V_{out}$  will transition to Low. When a N Pole approaches the pin 1 side,  $V_{out}$  will transition to High

# LF11215TMR Series

## TMR Bipolar Switch 17 Gauss 1.5uA Push Pull Sensor

### Absolute Maximum Ratings (@TA = +25°C, unless otherwise specified)

Symbol	Characteristics	Values	Unit
$V_{CC}$	Supply Voltage	7.0	V
$I_{OUTSINK} \text{ \& } I_{SOURCE}$	Output Current	9.0	mA
B	Magnetic Flux Density	4000	Gauss
$V_{ESD}$	ESD level(HBM)	4	kV
$T_A$	Operating Temperature	-40 ~ 125	°C
$T_{stg}$	Storage Temperature	-50 ~ 150	°C

**Note:** Stresses greater than the 'Absolute Maximum Ratings' specified above may cause permanent damage to the device. These are stress ratings only; functional operation of the device at these or any other conditions exceeding those indicated in this specification is not implied. Device reliability may be affected by exposure to absolute maximum rating conditions for extended periods of time.

### Electrical Characteristics (@TA= +25°C, Vcc = 3.0V)

Symbol	Characteristics	Min.	Typ.	Max.	Unit	Conditions
$V_{CC}$	Supply Voltage	1.8	3	5.5	V	Operating
$V_{OH}$	Output High Voltage	$V_{CC} - 0.3$	-	$V_{CC}$	V	-
$V_{OL}$	Output Low Voltage	-	-	0.2	V	-
$I_{CC}$	Supply Current	0.5	1.5	2	uA	Output Open
Freq	Response Frequency	-	1000	-	Hz	-



### Magnetic Characteristics (@TA = +25°C, Vcc = 3.0V)

Symbol	Characteristics	Min.	Typ.	Max.	Unit
$B_{OP}$	Operation Point	10	17	25	Gauss
$B_{RP}$	Release Point	-25	-17	-10	Gauss
$B_H$	Hysteresis		34		Gauss

# LF11215TMR Series

## TMR Bipolar Switch 17 Gauss 1.5uA Push Pull Sensor

### Pin Configuration and Sensing Direction of Magnetic Field



#### Part Marking Code:


Hxxx: H = LF11215TMR; xxx = Julian manufactured date; y = manufactured year

Moisture Sensitivity Level: Rating is 3

Pick and Place Nozzle: Samsung CN140 or equivalent

Pin Name	Pin No. SOT23-3	Pin Function
V <sub>OUT</sub>	2	Output
GND	3	Ground
V <sub>CC</sub>	1	Supply Voltage

### Part Numbering System




**Example:** LF11115 is Bipolar, Push Pull, 200 nA, X axis, 17 Gauss

**Note:** Every combination is NOT offered. Contact Littelfuse for availability.


# LF11215TMR Series

## TMR Bipolar Switch 17 Gauss 1.5uA Push Pull Sensor

### Soldering Profile for Lead-free packages




### Tape and Reel




$\varnothing A$	$\varnothing N$	$\varnothing B$	C	W1	W2	W3
178 $\pm$ 2	54 $\pm$ 2	13.2 $\pm$ 0.3	2.2 $\pm$ 0.3	8.4 $\pm$ 1.5/0.0	12 MAX	1.4 $\pm$ 0.4

**LF11215TMR Series**

TMR Bipolar Switch 17 Gauss 1.5uA Push Pull Sensor

**SOT23-3 Package Information**

Symbol	Dimensions in Millimeters			Dimensions in Inches		
	Min	Nom	Max	Min	Nom	Max
<b>A</b>	-	-	1.45	-	-	0.057
<b>A1</b>	0.00	-	0.15	0.000	-	0.006
<b>A2</b>	0.90	1.10	1.30	0.035	0.043	0.051
<b>A3</b>	0.60	0.65	0.70	0.024	0.026	0.028
<b>b</b>	0.39	-	0.49	0.015	-	0.019
<b>c</b>	0.12	-	0.19	0.005	-	0.007
<b>D</b>	2.85	2.95	3.05	0.112	0.116	0.120
<b>E</b>	2.60	2.80	3.00	0.102	0.110	0.118
<b>E1</b>	1.55	1.65	1.75	0.061	0.065	0.069
<b>e</b>	0.85	0.95	1.05	0.033	0.037	0.041
<b>e1</b>	1.80	1.90	2.00	0.071	0.075	0.079
<b>L</b>	0.35	0.45	0.60	0.014	0.018	0.024
<b>L1</b>	0.59REF			0.023REF		
<b>L2</b>	0.25BSC			0.01BSC		
<b>Ø</b>	0°	-	8°	0°	-	8°

**LF11215TMR Series****TMR Bipolar Switch 17 Gauss 1.5uA Push Pull Sensor****TMR Sensor Position (SOT23-3 Elements)**

**Important Notice** - Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.

**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).