


SiC Power MOSFET

$$I_{D25} = 25.5 \text{ A}$$


$$V_{DSS} = 1200 \text{ V}$$

$$R_{DS(on) \text{ max}} = 98 \text{ m}\Omega$$

Part number
 MCB20P1200LB



 E72873



Features / Advantages:

- High speed switching with low capacitances
- High blocking voltage with low $R_{DS(on)}$
- Easy to parallel and simple to drive
- Resistant to latch-up
- Real Kelvin source connection

Applications:

- Solar inverters
- High voltage DC/DC converters
- Motor drives
- Switch mode power supplies
- UPS
- Battery chargers
- Induction heating

Package: SMPD

- DCB isolated backside
- Isolation Voltage 2500 V
- Epoxy meets UL 94V-0
- RoHS compliant
- Advanced power cycling

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.


MOSFET				Ratings					
Symbol	Definitions	Conditions	min.	typ.	max.				
V_{DSS}	drain source breakdown voltage	$V_{GS} = 0\text{ V}, I_D = 100\ \mu\text{A}$	1200				V		
V_{GSM}	max transient gate source voltage		-10		+25		V		
V_{GS}	continous gate source voltage	recommended operational value	-5		+20		V		
I_{D25}	drain current	$V_{GS} = 20\text{ V}$			25.5		A		
I_{D80}					20.5		A		
I_{D100}					18		A		
R_{DSon}	static drain source on resistance	$I_D = 50\text{ A}; V_{GS} = 20\text{ V}$		80 155	98		mΩ mΩ		
$V_{GS(th)}$	gate threshold voltage	$I_D = 5\text{ mA}; V_{GS} = V_{DS}$	2.0	2.6 2.1	4.0		V V		
I_{DSS}	drain source leakage current	$V_{DS} = 1200\text{ V}; V_{GS} = 0\text{ V}$		2	100		μA		
I_{GSS}	gate source leakage current	$V_{DS} = 0\text{ V}; V_{GS} = 20\text{ V}$			250		nA		
R_G	internal gate resistance	$f = 1\text{ MHz}, V_{AC} = 25\text{ mV}, \text{ESR of } C_{ISS}$		4.6			Ω		
C_{ISS}	input capacitance			950			pF		
C_{OSS}	output capacitance	$V_{DS} = 1000\text{ V}; V_{GS} = 0\text{ V}; f = 1\text{ MHz}$	$T_{VJ} = 25^\circ\text{C}$	80			pF		
C_{RSS}	reverse transfer (Miller) capacitance			7.6			pF		
Q_g	total gate charge	$V_{DS} = 800\text{ V}; I_D = 40\text{ A}; V_{GS} = -5/20\text{ V}$	$T_{VJ} = 25^\circ\text{C}$		62		nC		
Q_{gs}	gate source charge				23		nC		
Q_{gd}	gate drain (Miller) charge				37		nC		
$t_{d(on)}$	turn-on delay time	Inductive switching $V_{DS} = 800\text{ V}; I_D = 20\text{ A}$ $V_{GS} = -5 / 20\text{ V}; R_G = 22\ \Omega$ (external) Freewheeling diode is Mosfet's body diode	$T_{VJ} = 25^\circ\text{C}$		19		ns		
t_r	current rise time				7		ns		
$t_{d(off)}$	turn-off delay time				66		ns		
t_f	current fall time				23		ns		
E_{on}	turn-on energy per pulse				0.41		mJ		
E_{off}	turn-off energy per pulse				0.21		mJ		
$E_{rec(off)}$	reverse recovery losses at turn-off				0.07		mJ		
$t_{d(on)}$	turn-on delay time			Inductive switching $V_{DS} = 800\text{ V}; I_D = 20\text{ A}$ $V_{GS} = -5 / 20\text{ V}; R_G = 22\ \Omega$ (external) Freewheeling diode is Mosfet's body diode	$T_{VJ} = 150^\circ\text{C}$		18		ns
t_r	current rise time						7		ns
$t_{d(off)}$	turn-off delay time						75		ns
t_f	current fall time		21				ns		
E_{on}	turn-on energy per pulse		0.49				mJ		
E_{off}	turn-off energy per pulse		0.20				mJ		
$E_{rec(off)}$	reverse recovery losses at turn-off		0.10				mJ		
R_{thJC}	thermal resistance junction to case	with heatsink compound; IXYS test setup					1.0		K/W
R_{thJH}	thermal resistance junction to heatsink					1.5		K/W	

Source-Drain Diode				Ratings			
Symbol	Definitions	Conditions	min.	typ.	max.		
V_{SD}	forward voltage drop	$I_F = 10\text{ A}; V_{GS} = -5\text{ V}$		3.3 3.1			V V
t_{rr}	reverse recovery time	$V_{GS} = -5\text{ V}; I_F = 20\text{ A}; V_R = 800\text{ V}$ Mosfet gate drive: $V_{GS} = -5 / 20\text{ V}; R_G = 22\ \Omega$	$T_{VJ} = 25^\circ\text{C}$		15		ns
Q_{RM}	reverse recovery charge (intrinsic diode)				0.20		μC
I_{RM}	max. reverse recovery current				23		A
di_F/dt	current slew rate				3650		A/μs
t_{rr}	reverse recovery time	$V_{GS} = -5\text{ V}; I_F = 20\text{ A}; V_R = 800\text{ V}$ Mosfet gate drive: $V_{GS} = -5 / 20\text{ V}; R_G = 22\ \Omega$	$T_{VJ} = 150^\circ\text{C}$		19		ns
Q_{RM}	reverse recovery charge (intrinsic diode)				0.42		μC
I_{RM}	max. reverse recovery current				35		A
di_F/dt	current slew rate				4120		A/μs

Note:

 When using SiC Body Diode the maximum recommended $V_{GS} = -5\text{V}$


Package SMPD			Ratings			
Symbol	Definitions	Conditions	min.	typ.	max.	
I_{RMS}	RMS current	wide terminal standard terminal			100 60	A A
T_{stg}	storage temperature		-55		150	°C
T_{op}	operation temperature		-55		150	°C
T_{VJ}	virtual junction temperature		-55		175	°C
Weight				8		g
F_c	mounting force with clip		40		130	N
$d_{Spp/App}$	creepage distance on surface /	terminal to terminal	1.6			mm
$d_{Spb/Appb}$	striking distance through air	terminal to backside	4.0			mm
V_{ISOL}	isolation voltage	t = 1 second t = 1 minute		3000 2500		V V
		50/60 Hz; RMS; $I_{ISOL} < 1$ mA				


Part number


M = Mosfet
 C = SiC MOSFET
 B = Generation 2
 20 = Current Rating [A]
 P = Phase leg
 1200 = Reverse Voltage [V]
 LB = SMPD-B

Digits
 1 to 19: Part #
 20 to 23: Date Code
 24 to 25: Assembly line
 26 to 31: Lot #
 32: Split Lot
 33 to 36: Individual #

Ordering	Part Name	Marking on Product	Delivering Mode	Base Qty	Ordering Code
Standard	MCB20P1200LB-TUB	MCB20P1200LB	Tube	20	MCB20P1200LB-TUB
Alternative	MCB20P1200LB-TRR	MCB20P1200LB	Tape&Reel	200	MCB20P1200LB-TRR

Outlines SMPD-B
A (8 : 1)


Dimensions in mm
 (1 mm = 0.0394")



Curves




Fig. 1 Typical output characteristics (-25°C)




Fig. 2 Typical output characteristics (25°C)




Fig. 3 Typical output characteristics (150°C)




Fig. 4 $R_{DS(on)}$ normalized vs. junction temperature T_{VJ}




Fig. 5 $R_{DS(on)}$ versus drain current




Fig. 6 $R_{DS(on)}$ versus junction temperature T_{VJ}

Curves




Fig. 7 Norm. breakdow V_{DSS} & treshhold voltage V_{TH} versus junction temperature T_{VJ}




Fig. 8 Typical transfer characteristics




Fig. 9 Typical forward transconductance




Fig. 10 Forward voltage drop of intrinsic diode versus V_{DS} measured at -55°C




Fig. 11 Forward voltage drop of intrinsic diode versus V_{DS} measured at 25°C




Fig. 12 Forward voltage drop of intrinsic diode versus V_{DS} measured at 150°C


Curves


Fig. 13 Typical switching energy versus drain current




Fig. 14 Typical switching energy versus temperature




Fig. 15 Typical switching energy versus external gate resistor




Fig. 16 Typical switching time versus external gate resistor




Fig. 17 Typical turn on gate charge, trendline




Fig. 18 Typical transient thermal impedance