

# TPSMA6L-E Series

## Surface Mount – 600 W



### Agency Approvals

Agency	Agency File Number
	E230531

### Maximum Ratings and Thermal Characteristics

( $T_A=25\text{ }^\circ\text{C}$  unless otherwise noted)

Parameter	Symbol	Value	Unit
Peak Pulse Power Dissipation with 10/1000 $\mu\text{s}$ exponential pulse	$P_{PPM}$	600	W
Peak Forward Surge Current 8.3 ms. (Jedec Method) (Note 1)	$I_{FSM}$	100	A
Max. Forward Voltage Drop at $I_F = 25\text{ A}$	$V_F$	3.5	V
Operating Junction Temperature Range	$T_J$	-65 to 185	$^\circ\text{C}$
Storage Temperature Range	$T_{STG}$	-65 to 185	$^\circ\text{C}$
Typical Thermal Resistance Junction to Lead	$R_{th(j-l)}$	20	$^\circ\text{C/W}$

#### Notes:

1. Mounted on 0.31 x 0.31" (8.0 x 8.0 mm) copper pads to each terminal

### Functional Diagram



## Description

Littelfuse TPSMA6L-E Series of Transient Voltage Suppression (TVS) Diodes can provide secondary transient voltage protection from transients induced by load dump and other transient voltage events for sensitive electronics. The TPSMA6L-E Series offers superior electrical performance in a small footprint SOD128 package, allowing designers to upgrade their circuit protection without altering their existing design footprint or provide more robust protection in new circuit layouts.

## Features

- Top-glass technology for enhanced reliability TVS
- Low profile package (SOD128)
- Ideal for automated placement
- 600 W peak pulse power capability with a 10/1000  $\mu\text{s}$  waveform, repetitive rate (duty cycle): 0.01 %
- Excellent clamping capability
- Very fast response time
- Low incremental surge resistance
- Available in uni-directional
- Solder dip 260  $^\circ\text{C}$ , 10s
- AEC-Q101 qualified and PPAP capable
- Component in accordance to RoHS 2011/65/EU and WEEE 2002/96/EC
- Meets MSL level 1, per J-ED-020, LF maximum peak of 260  $^\circ\text{C}$
- Manufactured outside China and Taiwan

## Applications

Designed to use in the harsh automotive environments for low voltage high frequency inverters, freewheeling, DC-to-DC electronic application.


### Physical Specifications

<b>Weight</b>	0.0180 grams
<b>Case</b>	SOD-128. Epoxy meets UL 94V-0 flammability rating.
<b>Polarity</b>	Color band denotes cathode end.
<b>Terminal</b>	Matte tin plated leads, solderable per MIL-ED-750 Method 2026, J-ED-002 and JESD22-B102. Meets JESD 201 class 1A whisker test.

# TPSMA6L-E Series

## Surface Mount – 600 W

### Electrical Characteristics ( $T_A=25\text{ }^\circ\text{C}$ unless otherwise noted)

Part Number	Marking Code	Maximum Reverse Leakage Current $I_{RM}$ at $V_{RM}$		Breakdown Voltage $V_{BR}$ at $I_R$ (V) <sup>(1)</sup>				Max. Clamping Voltage $V_{CL}$ at $I_{PP}$ max. 1ms. Expo.		Agency Approval 
		( $\mu\text{A}$ )	(V)	Min.	Nom.	Max.	(mA)	(V)	(A)	
TPSMA6L5V0A-E	0A	500	5.0	6.40	6.70	7.00	10	9.0	65.2	X
TPSMA6L6V0A-E	0B	250	6.0	6.67	7.02	7.37	10	10.3	58.3	X
TPSMA6L6V5A-E	0C	250	6.5	7.22	7.60	7.98	10	11.2	53.6	X
TPSMA6L7V0A-E	0D	100	7.0	7.78	8.20	8.60	1	12.0	50.0	X
TPSMA6L7V5A-E	0E	50	7.5	8.33	8.77	9.21	1	12.9	46.5	X
TPSMA6L8V0A-E	0F	25	8.0	8.89	9.36	9.83	1	13.6	44.1	X
TPSMA6L8V5A-E	0G	10	8.5	9.44	9.92	10.40	1	14.4	41.7	X
TPSMA6L9V0A-E	0H	1	9.0	10.00	10.55	11.10	10	15.4	39.0	X
TPSMA6L10A-E	0I	1	10.0	11.10	11.70	12.30	10	17.0	35.3	X
TPSMA6L11A-E	0J	1	11.0	12.20	12.85	13.50	10	18.2	33.0	X
TPSMA6L12A-E	0K	1	12.0	13.30	14.00	14.70	10	19.9	30.2	X
TPSMA6L13A-E	0L	0.5	13.0	14.40	15.15	15.90	1	21.5	27.5	X
TPSMA6L14A-E	0M	0.5	14.0	15.60	16.40	17.20	1	23.2	27.9	X
TPSMA6L15A-E	0N	0.5	15.0	16.70	17.60	18.50	1	24.4	24.6	X
TPSMA6L16A-E	0O	0.5	16.0	17.80	18.75	19.70	1	26.0	23.1	X
TPSMA6L17A-E	0P	0.5	17.0	18.90	19.90	20.90	1	27.6	21.7	X
TPSMA6L18A-E	0Q	0.5	18.0	20.00	21.00	22.10	1	29.2	20.5	X
TPSMA6L20A-E	0R	0.5	20.0	22.20	23.35	24.50	1	32.4	18.5	X
TPSMA6L22A-E	0S	0.5	22.0	24.40	25.60	26.90	1	35.5	16.9	X
TPSMA6L24A-E	0T	0.5	24.0	26.70	28.10	29.50	1	38.9	15.4	X
TPSMA6L26A-E	0U	0.5	26.0	28.90	30.40	31.90	1	42.1	14.2	X
TPSMA6L28A-E	0X	0.5	28.0	31.10	32.80	34.40	1	45.4	13.2	X
TPSMA6L30A-E	0Y	0.5	30.0	33.30	35.10	36.80	1	48.4	12.4	X
TPSMA6L33A-E	0Z	0.5	33.0	36.70	38.70	40.60	1	53.3	11.3	X
TPSMA6L36A-E	9E	0.5	36.0	40.00	42.10	44.21	1	58.1	10.3	X
TPSMA6L40A-E	9F	0.5	40.0	44.40	46.80	49.10	1	64.5	9.3	X
TPSMA6L43A-E	9G	0.5	43.0	47.80	50.30	52.80	1	69.4	8.6	X
TPSMA6L45A-E	9H	0.5	45.0	50.00	52.65	55.30	1	72.7	8.3	X
TPSMA6L48A-E	9I	0.5	48.0	53.30	56.10	58.90	1	77.4	7.8	X
TPSMA6L51A-E	9J	0.5	51.0	56.70	59.70	62.70	1	82.4	7.3	X
TPSMA6L54A-E	9K	0.5	54.0	60.00	63.15	66.30	1	87.1	6.9	X
TPSMA6L58A-E	9L	0.5	58.0	64.40	67.80	71.20	1	93.6	6.4	X
TPSMA6L60A-E	9M	0.5	60.0	66.70	70.20	73.70	1	96.8	6.2	X
TPSMA6L64A-E	9N	0.5	64.0	71.10	74.85	78.60	1	103.0	5.8	X

#### Notes:

1. Tested with pulses Pulse test:  $t_p \leq 50\text{ ms}$ ;  $\delta < 2\%$

# TPSMA6L-E Series

## Surface Mount – 600 W

### Ratings and Characteristic Curves ( $T_A=25\text{ }^\circ\text{C}$ unless otherwise noted)

Figure 1 - Pulse Waveform




Figure 2 - Pulse Power or Current vs. Initial Junction Temperature




Figure 3 - Peak Pulse Power Rating Curve







Figure 4 - Typical Junction Capacitance



### Part Numbering System




### Part Marking System



# TPSMA6L-E Series

## Surface Mount – 600 W


### Dimensions - SOD128 Package



### Packaging Options

Part number	Component Package	Quantity	Packaging Option	Packaging Specification
TPSMA6LxxX-E	SOD-128	10000	13" diameter tape and reel	EIA RS-481

### Tape and Reel Specification



**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.