

REVISION		
REV	DATE	DESCRIPTION
A	11/1/2011	502834ERP - RELEASE MRY

SPECIFICATIONS:

VOLTAGE RATING: 600V

AMPERE RATING: 175 AMP CU; 135 AMP AL



SUGGESTED TORQUE (LINE): 13.6 N-m (120 IN-LBS) 2/0-6 AWG
4.5 N-m (40 IN-LBS) 8-14 AWG

SUGGESTED TORQUE (LOAD): 13.6 N-m (120 IN-LBS) 2/0-6 AWG
4.5 N-m (40 IN-LBS) 8-14 AWG

WIRE RANGE (LINE): 2/0-14 AWG Cu/Al
SOLID/STRANDED

WIRE RANGE (LOAD): 2/0-14 AWG Cu/Al
SOLID/STRANDED

APPROVALS: UL RECOGNIZED (FILE NO. E309688)
CSA CERTIFIED (FILE NO. 007316_0_000)

●	DENOTES CRITICAL CHARACTERISTICS.		
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE		
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.		
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.		B
MATL SPEC		FINISH	
DRW MYORK	DATE 7/18/2011	SCALE NTS	FINISH GOOD WT GRAMS/PIECE
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994			
3RD ANGLE PROJECTION 			
TITLE LFS2572 OUTLINE			
 Littelfuse® CHICAGO, ILLINOIS 60631		REVISION A	DRWG NO. OL-LFS2572 SHEET 1 OF 1

