

PART NUMBER	FIGURE	"A"	"B"	"C"	"D"	LEAD "A" COLOR	LEAD "B" COLOR	INSULATION TYPE	WIRE SIZE	RATING MARK	PKG QTY
OFHJ1001G	1	102.0±5.0	102.0±5.0	9.0±2.0	9.0±2.0	RED	RED	GXL (STANDARD)	10 AWG	40A	250
OFHJ1002G	1	102.0±5.0	102.0±5.0	9.0±2.0	9.0±2.0	RED	RED	GXL (STANDARD)	8 AWG	60A	250
OFHJ1002L	1	102.0±5.0	102.0±5.0	9.0±2.0	9.0±2.0	RED	RED	GXL (STANDARD)	8 AWG	60A	50
OFHJ2001G	2	102.0±5.0	102.0±5.0	9.0±2.0	9.0±2.0	RED	RED	GXL (STANDARD)	10 AWG	40A	250
OFHJ2002G	2	102.0±5.0	102.0±5.0	9.0±2.0	9.0±2.0	RED	RED	GXL (STANDARD)	8 AWG	60A	250
OFHJ2002L	2	102.0±5.0	102.0±5.0	9.0±2.0	9.0±2.0	RED	RED	GXL (STANDARD)	8 AWG	60A	50

- NOTES:
- HOLDER MATERIAL: BLACK TPV MATERIAL
 - CONTACTS: TIN-PLATED COPPER ALLOY
 - WIRE SIZE & LENGTH: SEE CHART
 - MAX TEMPERATURE: 125° C
 - RATING MARKING: SEE CHART
 - FUSE HOLDERS SHOULD NOT BE PLACED UNDER TENSION IN FINAL APPLICATION.
 - ALL PARTS PACKAGED BULK IN QTY SHOWN.

LTR	DATE	REVISION	CHK	APD
A	11/19/09	000847ER-RELEASED	CAD	
B	08/17/12	505869ECA-REMOVAL OF MOUNTING HOLE	OPL	
C	04/16/15	511793ECA-COMPILED ALL OFHJ HOLDERS ONTO ONE PRINT; ADDED PKG NOTES; ADDED BRACKET VERSION VIEWS; PRINT NAME CHANGED FROM OFHJ1000G TO OFHJ00000. FYUE		




FIGURE 1. STANDARD HOLDER







FIGURE 2. HOLDER WITH MOUNTING BRACKET



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES											
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.											
	DENOTES CRITICAL CHARACTERISTICS.										
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE										
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS										
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE										
COPIES TO		MATL SPEC									
1	9	18	 FINISH								
2	10	19									
3	12	20									
4	13	21									
5	14	23									
6	15	33									
7	16	43									
8	17	53									
		DRW	CAD	DATE	11/19/09	SCALE	1:1				
		CHK		DATE		SUPER DR					
		APPD		DATE		FINISH GOOD WT					
							GRAMS/PIECE				
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)											
DIMENSION	0.5 - 3		UP TO 3 OVER 3 - 6		UP TO 6 OVER 6 - 30		UP TO 30 OVER 30 - 120		UP TO 120 OVER 120 - 400		
TOLERANCE	±0.1		±0.1		±0.2		±0.3		±0.5		
3RD ANGLE PROJECTION				TITLE							
				INLINE JCASE HOLDER WITHOUT COVER							
				[REVISION]		DRWG. NO.		OUTLINE			
DES PLAINES, ILLINOIS 60016				C		OL-OFHJ00000					

METRIC
ASSEMBLY

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED