






DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.								
linear dimensions								
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000		
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3		
angle (for range of lengths)								
up to 10		>10 50		>50 120		>120 400		
±1°30'		±1°		±0°30'		±0°15'		
	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL							
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL							
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE							
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS							
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE							
NAME		DATE		 <b>Littelfuse®</b> <b>Expertise Applied   Answers Delivered</b>				
DRAWN		L. Dal Molin					10-Jun-22	
CHECKED		-					-	
							-	
FORM NO: CVP-PE40-0013 REV A				<b>TITLE</b> <b>MANUAL BATTERY SWITCH HANDLE</b> <b>M10</b>				
FIRST ANGLE PROJECTION								
				SIZE: <b>A3</b> DWG. NO. <b>OL-08080670</b> OUTLINE REV. <b>A</b>				
DO NOT SCALE DRAWING				SCALE 1:2		SHEET 1 OF 1		