



PART NO.
GDB61753Z

LTR	DATE	REVISION	CHK	APD
A	4/17/18	519180GCP - RELEASE MRY		









NOTES:

1. AGENCY INFORMATION:
   UL FILE NO. E309688
2. MATERIALS:
   INSULATOR-THERMOPLASTIC
   CONNECTOR-BRASS
3. TERMINATION:
   LINE: 8AWG-2/0
   LOAD: 4-14 AWG
4. RATINGS:
   600V
   MAXIMUM AMP PER POLE-175A
5. TORQUE:
   LINE: 35.5 IN-LB
   LOAD: 17.5 IN-LB

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.	
●	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS,-MINIMUM CPK VALUE
⟨ST⟩	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.
CP	DENOTES CP DIMENSIONS,-MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE. C

COPIES TO	MATL SPEC		
1 9 18 2 10 19 3 12 20 4 13 21 5 14 23 6 15 33 7 16 43 8 17 53	FINISH		
	DRW M YORK	DATE 4/9/18	SCALE
	CHK	DATE	SUPER DR
	APPD	DATE	RAW STK WT LBS/M

TITLE
GDB6175 SERIES DISTRIBUTION BLOCK OUTLINE

Littelfuse®
CHICAGO, ILLINOIS 60631

REVISION	DRWG. NO.	FINAL
A	OL-GDB6175	

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED