


DST1045S-A




**Description**

Littelfuse DST series Ultra Low VF Schottky Barrier Rectifier is designed to meet the general requirements of commercial and industry applications by providing high temperature, low leakage, and lower VF products.

It is suitable for high frequency switching mode power supply applications, such as free-wheeling and polarity protection diodes.

**Pin out**



**Features**

- Ultra low forward voltage drop
- High frequency operation
- High junction temperature capability
- Trench MOS Barrier Schottky technology
- Single die in TO-277B Package
- High Reliability application and AEC-Q101 qualified

**Applications**

- Switching mode power supply
- DC/DC converters
- Free-Wheeling diodes
- Polarity Protection Diodes

**Maximum Ratings**

Parameters	Symbol	Test Conditions	Max	Unit
Peak Inverse Voltage	$V_{RWM}$	-	45	V
Average Forward Current *	$I_{F(AV)}$	50% duty cycle @ $T_c = 125^\circ\text{C}$ rectangular wave form	10	A
Peak One Cycle Non-Repetitive Surge Current	$I_{FSM}$	8.3 ms, half Sine pulse	150	A

\* Mounted on 30 mm x 30 mm pad areas aluminum PCB

**Electrical Characteristics**

Parameters	Symbol	Test Conditions	Typ	Max	Unit
Forward Voltage Drop *	$V_{F1}$	@5A, Pulse, $T_j = 25^\circ\text{C}$	0.43	0.51	V
		@10A, Pulse, $T_j = 25^\circ\text{C}$	0.49	0.57	
	$V_{F2}$	@5A, Pulse, $T_j = 125^\circ\text{C}$	0.32	0.43	
		@10A, Pulse, $T_j = 125^\circ\text{C}$	0.41	0.50	
Reverse Current *	$I_{R1}$	@ $V_R = \text{rated } V_R, T_j = 25^\circ\text{C}$	0.017	0.80	mA
	$I_{R2}$	@ $V_R = \text{rated } V_R, T_j = 125^\circ\text{C}$	15	100	
Junction Capacitance	$C_T$	@ $V_R = 5\text{V}, T_c = 25^\circ\text{C}, f_{SIG} = 1\text{MHz}$	656	-	pF

\* Pulse Width < 300µs, Duty Cycle < 2%

### Thermal-Mechanical Specifications


Parameters	Symbol	Test Conditions	Max	Unit
Junction Temperature	$T_J$	-	-55 to +150	°C
Storage Temperature	$T_{stg}$	-	-55 to +150	°C
Thermal Resistance Junction to Ambient	$R_{\theta JA}$	DC operation	75	°C/W
Typical Thermal Resistance Junction to Lead	$R_{\theta JL}^*$	DC operation	3.5	°C/W
Approximate Weight	wt	-	0.08	g
Case Style	TO-277B			

1. Free air, mounted on recommended copper pad area; thermal resistance  $R_{\theta JA}$  - junction to ambient


2. Mounted on 30 mm x 30 mm pad areas aluminum PCB; thermal resistance  $R_{\theta JL}$  - junction to lead

\* Lead temperature monitored at the cathode pin


**Figure 1: Forward Current Derating Curve**



**Figure 2: Forward Power Loss Characteristics**



**Figure 3: Typical Instantaneous Forward Voltage Characteristics**



**Figure 4: Typical Reverse Characteristics**






Figure 5: Typical Junction Capacitance




Dimensions-TO-277B



Symbol	Millimeters		
	Min	Typ	Max
A	6.30	6.50	6.70
B	5.28	5.38	5.48
C	3.88	3.98	4.08
D	2.90	3.05	3.20
E	3.40	3.55	3.70
F	4.20	4.40	4.60
G	1.70	1.80	1.90
I	1.74	1.84	1.94
J	0.65	0.85	1.05
K	0.85	0.90	0.95
L	0.95	1.10	1.25
M	0.20	0.25	0.30
N	0.25	0.40	0.55
O	4.00	4.05	4.25

Part Numbering and Marking System

Mounting Pad Layout



DST = Component Type  
 10 = Forward Current (10A)  
 45 = Reverse Voltage (45V)  
 S = Package Type  
 A = AEC-Q101 Qualified Component  
 LF = Littelfuse  
 YY = Year  
 WW = Week  
 L = Lot Number

**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.