


PART NUMBER	COVER OPENINGS
04980915ZXT	E F



LETTER DESIGNATIONS REFER TO POSITIONS OF AVAILABLE COVER OPENINGS. (SEE CHART)

NOTES:

- TAB OF COVER TIE IS INSERTED INTO HOLE IN BASE.
- TORQUE REQUIRED FOR HEX NUT TO BE 4.0 - 5.0 NEWTON METERS (35-44 IN-LBS).
- CAP SCREW AND NUTS - M5 X 0.8 - AND WASHERS, STEEL, ZINC PLATE WITH TRIVALENT CHROMATE, LEACHED AND SEALED, INTEGRAL TORQUE CONTROL LUBRICANT FINISH. (MEETS 96 HR. ASTM STD. B-117 SALT SPRAY REQ.).
- HOLDER MEETS L/F VALIDATION TEST SPEC. VS-005004.

METRIC

NO		COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL					
COPIES TO		MATERIAL SPEC			
LTR		DATE		REVISION	
A	05/25/05	61735 - RELEASE		DJG	
B	06/08/07	85460D-REDRAWN IN UG, ADDED TOLERANCE TO DIMENSIONS, 7.24 WAS 8.19 GMB			
FINISH		TOLERANCE UNLESS OTHERWISE SPECIFIED			
DRW		DATE		SCALE	
CHK		DATE		SUPER DR	
APPD		DATE		FINISH GOOD WT	
ONE PLACE DEC +/- .25		THREE PLACE DEC +/- .100		GRAMS/PIECE	
TWO PLACE DEC +/- .13		ANGULAR +/- 1°			
3RD ANGLE PROJECTION		TITLE		MIDI FUSE HOLDER	
REVISION		DRWG. NO.		OUTLINE	
B		04980915ZXT			