






PART NO.
GDB60801Z

LTR	DATE	REVISION	CHK	APD
A	4/17/18	519180GCP - RELEASE MRY		



- NOTES:
1. AGENCY INFORMATION:
UL FILE NO. E309688
 2. MATERIALS:
INSULATOR-THERMOPLASTIC
CONNECTOR-BRASS
 3. TERMINATION:
LINE: 8-14 AWG
LOAD: (2) 8-4 AWG
(4) 10-14 AWG
 4. RATINGS:
600V
MAXIMUM AMP PER POLE-80A
 5. TORQUE:
LINE: 13.5 IN-LB
LOAD: 8-4 AWG 13.5 IN-LB
10-14 AWG 7.2 IN-LB

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.			
●	DENOTES CRITICAL CHARACTERISTICS.		
CPK	DENOTES CPK DIMENSIONS,-MINIMUM CPK VALUE		
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.		
CP	DENOTES CP DIMENSIONS,-MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.		
COPIES TO		MATL SPEC	
1	9	18	FINISH
2	10	19	
3	12	20	
4	13	21	
5	14	23	
6	15	33	
7	16	43	
8	17	53	
DRW M YORK		DATE 04/09/18	SCALE
CHK		DATE	SUPER DR
APPD		DATE	RAW STK WT
			LBS/M
TITLE			
80A IEC DISTRIBUTION BLOCK OUTLINE			
Littelfuse® CHICAGO, ILLINOIS 60631		REVISION A	DRWG. NO. DL-GDB6080
		FINAL	

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED