



**MOUNTING SPECS:**

STUD SIZE: M8 x 1.25 - 6H  $\varnothing$  8.0 [0.31]





STUD TORQUE (REFERENCE ONLY): 13 - 20 Nm

| REVISION |          |  |
|----------|----------|--|
| REV      | DATE     | DESCRIPTION                                |
| A        | 4/20/20  | 522234GCP - RELEASE MRY                    |
| B        | 10/25/23 | 526838ECP/D - ADD VIEW W/O MICROSWITCH MRY |

**FUSE WITH MICROSWITCH**



**FUSE**



**FUSE WITH MICROSWITCH**

FOR REFERENCE ONLY

|     |  |
|-----|--|
| <S> | CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE   |
| ●   | DENOTES CRITICAL CHARACTERISTICS.  |
| CPK | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE   |
| ST  | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS. |
| CP  | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.               |

|           |                |           |                            |
|-----------|----------------|-----------|----------------------------|
| MATL SPEC | FINISH         |           |                            |
| DRW myork | DATE 4/14/2020 | SCALE NTS | FINISH GOOD WT GRAMS/PIECE |

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

|                      |  |
|----------------------|--|
| 3RD ANGLE PROJECTION |  |
|----------------------|--|

TITLE PSX SIZE 1XL FLUSH MOUNT (FL) FUSE OUTLINE

|  |               |                             |              |
|--|---------------|-----------------------------|--------------|
| <b>Littelfuse</b><br>CHICAGO, ILLINOIS 60631 | REVISION<br>B | DRWG NO.<br>OL-PSX1XLFL0000 | SHEET 1 OF 1 |
|--|---------------|-----------------------------|--------------|