



[illegible]

- NOTES:
1. MATERIAL:
 - BASE/COVER: PA66, 30%GF, BLACK
 - TPA: PA, BLUE
 - SEAL: SILICONE RUBBER, GREEN
 2. TORQUE RATING: 4-6 Nm USING M6 BOLT & LOCK WASHER.
 3. FUSE RATING: 30A PER CIRCUIT.
 4. OPERATING & STORAGE TEMPERATURE: -40°C TO 125°C
 5. IP SEALING CLASS PER IEC60529 IP66 & IP67.
 6. TERMINAL RATING PER USCAR 2 SECTION 5.4.1.3 USING PROPER DELPHI METRI-PACK TERMINALS (SEALED/TANGLESS).
 7. TPA RETENTION PER USCAR 2 SECTION 5.4.4.4
 8. MAX. CONTINUOUS CURRENT: 250A FOR ENTIRE FUSEHOLDER.

-					
-					
-					
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M	
BILL OF MATERIAL					
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES					
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.					
	DENOTES CIRCULAR CHARACTERISTICS.				
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE				
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS				
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE				
COPIES TO		MATL SPEC			
1 9 18		SEE NOTE			
2 10 19		FINISH			
3 12 20		NONE			
4 13 21		DRW	FYUE	DATE	16/Sep/15
5 14 23		CHK		DATE	SUPER DR
6 15 33		APPD		DATE	FINSH GOOD WT
7 16 43		GRAMS/PIECE			
8 17 53		TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)			
DIMENSION		0.5 - 3	UP TO 3	OVER 3 - 6	UP TO 6
		30 - 6	OVER 6 - 30	UP TO 30	OVER 30 - 120
		120 - 400	UP TO 120	OVER 120 - 400	UP TO 400
TOLERANCE		+0.1		+0.1	
		+0.2		+0.3	
				+0.5	
3RD ANGLE PROJECTION		TITLE			
		60 WAY FUSE HOLDER			
		REVISION		DRWG. NO.	
		B		PDM71003ZXM	
OUTLINE					
REF. PLAINING JULY 1995 60016					

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED

METRIC

ASSEMBLY