


TERMINAL	NO. WIRES PER TERMINAL	WIRE RANGE	SOLID WIRE	STRANDED WIRE
A	1	#12-8	X	X
	2	#12	X	X

REVISION		
REV	DATE	DESCRIPTION
A	1/16/23	526124GCP - RELEASE MRY



RECOMMENDED CRIMP TOOL:
A TERMINAL- T&B WT161M,
1 CRIMP

STRIP WIRES 1".
CRIMP 1/4" FROM END

NOTES:

- PRODUCT IS UL RECOGNIZED
- MATERIAL TYPE: BODY: BLACK, FLAME RETARDANT, GLASS FIBER REINFORCED, POLYESTER RESIN
TERMINALS: TIN-PLATED COPPER
FUSE CLIPS: TIN-PLATED BRASS
SPRING: STAINLESS STEEL
SCREW: ZINC-PLATED STEEL

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE			
●	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.			
MATL SPEC			FINISH	
DRW myork	DATE 1/13/23	SCALE NTS	FINISH GOOD WT GRAMS/PIECE	
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994				
3RD ANGLE PROJECTION	TOLERANCE UNLESS OTHERWISE SPECIFIED ONE PLACE DEC ± .25 [.01] FRACTION ± TWO PLACE DEC ± .100 [.004] ANGULAR ±1°			
TITLE OLEX00AAX OUTLINE				
Littelfuse® CHICAGO, ILLINOIS 60631		REVISION A	DRWG NO. OL-OLEXAA	SHEET 1 OF 1