

0.25	.010
0.81	.032
1.82	.072
2.28	.090
3.81	.150
4.31	.170
4.57	.180
4.82	.190
6.09	.240
6.35	.250
7.36	.290
13.20	.520
17.01	.670
20.82	.820
23.36	.920
26.92	1.060
28.78	1.330
35.05	1.390
43.68	1.720

OFF
M & M

RUN

ON
S & S

Technical drawing of a component, likely a valve or fitting, showing dimensions and a cross-section view. The component is labeled "COLE HERSEE CO. BOSTON USA".

Dimensions (in inches):

- Overall height: 3.68
- Top section height: 4.31 (with a note "4.57" below it)
- Top section diameter: 4.82 R
- Top section hole diameter: .431 (with a note "DIA (2 HOLES)" below it)
- Section height: 35.05
- Section diameter: 23.36
- Section hole diameter: 17.01
- Bottom section height: 13.20
- Bottom section diameter: 20.82

The drawing includes a cross-section view of the top section, showing internal features and a central hole. The text "COLE HERSEE CO. BOSTON USA" is visible on the side of the component.

-0.81X1.82 KEYWAY

Confidential property of Cole Hersee

METRIC

LEVER, BRASS, CHROME PLATE

HEX NUT, STEEL

15/32-32UNS-2ATHD

HOUSING, ZINC DIE CAST, BRIGHT ZINC

TERMINAL, STEEL (4 REQ'D.)

SCREW-SEMS, 8-32UNC-2A X 6.35 LG., STEEL (4 REQ'D.)

SPRING UN POS.

6.09

7.36

26.92 REF

7.36

2.28

33.78 REF

3.81 REF

NOTES

1. SILVER CONTACT SURFACES.
2. MELAMINE LINER.
- ③ 3. ALL STEEL PARTS PLATED
- ④ 4. HEX NUT & SCREWS TO BE BAGGED

DO NOT SCALE

[illegible]