



| REVISION |         |                                    |
|----------|---------|------------------------------------|
| REV      | DATE    | DESCRIPTION                        |
| A        | 6/25/18 | 519469GCP - RELEASE PER EM3026 MRY |
| B        | 3/31/22 | 524923ECP/D - ADD TOLERANCES MRY   |



|   |  |               |  |
|---|--|---------------|--|
| ●   | DENOTES CRITICAL CHARACTERISTICS.  |               |  |
| CPK   | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE   |               |  |
| ⬮   | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS. |               |  |
| CP  | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.               |               |  |
| MATL SPEC   |  | FINISH        |  |
| DRW MYORK   | DATE 4/18/2018   | SCALE NTS     | FINISH GOOD WT GRAMS/PIECE               |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994 |  |               |  |
| 3RD ANGLE PROJECTION  |  |               |  |
| <b>TITLE</b><br>1500VDC SIZE 3L W/ S-BLADE PHOTOVOLTAIC FUSE W/ MICROSWITCH INTERFACE OUTLINE   |  |               |  |
|  <b>Littelfuse®</b><br>CHICAGO, ILLINOIS 60631   |  | REVISION<br>B | DRWG NO. OL-SPNH.X3LDLMS<br>SHEET 1 OF 1 |