



*BODY - GLASS FILLED THERMOPLASTIC: COLOR-BLACK
*COVER - THERMOPLASTIC: COLOR-BLACK
*HARDWARE - 5M THREADED STUDS & NUTS AND STEEL
LOCKWASHER WITH ZINC AND TRIVALENT CHROMATE,
LEACHED AND SEALED, INTEGRAL TORQUE CONTROL
LUBRICANT FINISH (MEETS ASTM STANDARD B-117,
96 HR. SALT SPRAY REQUIREMENTS).

*HARDWARE - 5M THREADED STUDS & NUTS WITH INTEGRAL LOCKWASHER WITH ZINC AND TRIVALENT CHROMATE, LEACHED AND SEALED, INTEGRAL TORQUE CONTROL LUBRICANT FINISH (MEETS ASTM STANDARD B-117, 96 HR. SALT SPRAY REQUIREMENTS).



Technical drawing of the bracket fastener assembly, showing front and side views with dimensions in inches and millimeters.

Front View Dimensions:

- Top width: 11.56 [455]
- Top width (alternative): .35
- Top width (alternative): REF.
- Height: 1.90 [.075]
- Bottom width: 15.48 [.609]
- Bottom width (alternative): REF.
- Overall bottom width: 29.36 [1.16]

Side View Dimensions:

- Height: 24.87 [.98]
- Overall length: 51.36 [2.02]
- Component: BRACKET FASTENER

1. TAB COVER TIE IS INSERTED INTO HOLE IN BASE.
2. TORQUE REQUIRED FOR TOP NUT (NOT SHOWN) TO BE 4.0 - 5.0 NEWTON METERS (35-44 IN-LBS).
3. CAP SCREW AND JAM NUT - M5 X 0.8 STEEL, ZINC PLATE WITH TRIVALENT CHROMATE, LEACHED AND SEALED, INTEGRAL TORQUE CONTROL LUBRICANT FINISH. (MEETS 96 HR. ASTM STD. B-117 SALT SPRAY REQ.).
4. HOLDER MEETS L/F VALIDATION TEST SPEC. VS-005004.

METRIC

[illegible]