



1-20A



25-30A



35-60A

| REVISION |            |   |
|----------|------------|---|
| REV      | DATE       | DESCRIPTION   |
| A        | 09/06/2013 | 509410GCP - RELEASE PER SALES RELEASE EM2461 MRY                        |
| B        | 10/28/2013 | 509611ECP/D - ADD 25-30A, CORRECT LENGTH MRY                            |
| C        | 11/21/2013 | 509817ECP/C - CHANGE FROM 6-15A TO 6-20A MRY                            |
| D        | 04/13/2015 | 514186ECP/D - ADD TOLERANCES, UPDATE 30A DESIGN, ADD DATA SHEET REV MRY |
| E        | 08/17/2015 | 514769ECP/D - UPDATE DATA SHEET REVS MRY                                |
| F        | 08/30/2016 | 516307ECP/D - UPDATE SPXY DATA SHEET REV MRY                            |
| G        | 6/6/17     | 517430ECP/D - REMOVE DATA SHEET REVISION, CHG 6-20A TO 4-20A MRY        |
| H        | 9/5/17     | 518050ECP/C - CHG 4-20A TO 1-20A MRY                                    |
| J        | 9/16/19    | 521247ECP/D - ADD 35-60A MRY  |

|           |  |           |                            |
|-----------|--|-----------|----------------------------|
| ●         | DENOTES CRITICAL CHARACTERISTICS.  |           |                            |
| CPK       | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE   |           |                            |
| (ST)      | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS. |           |                            |
| CP        | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.               |           |                            |
| MATL SPEC |  | FINISH    |                            |
| DRW MYORK | DATE 1/18/2013   | SCALE NTS | FINISH GOOD WT GRAMS/PIECE |

**B**

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994



**TITLE** 1500VDC PHOTOVOLTAIC FUSE

|  |          |            |              |
|--|----------|------------|--------------|
|  | REVISION | DRWG NO.   | SHEET 1 OF 1 |
|  | J        | OL-SPXV000 |              |