




PART NUMBER	"A"	"B"	"C"	"D"	LEAD "A" COLOR	LEAD "B" COLOR
FHAC0003ZXJA	89.3±5 [3.516]	89.3±5 [3.516]	6.35±2 [0.25]	6.35±2 [0.25]	RED	RED
FHAC0003ZXJB	89.3±5 [3.516]	89.3±5 [3.516]	6.35±2 [0.25]	6.35±2 [0.25]	RED WITH BLUE STRIPE	RED WITH BLUE STRIPE

LTR	DATE	REVISION	CHK	APD
A	11/21/07	000218ER-RELEASE FHAC0003ZXJA AND FHAC0003ZXJB DHM		
B	04/30/15	511837ECA-REMOVE MODEL NAME OF HOLDER MATERIAL FYUE		

NOTES:
1. HOLDER MATERIAL: BLACK TPV
2. CONTACTS: COPPER ALLOY TIN-PLATED
3. WIRE: 14 AWG STRANDED COPPER, 125°C RATED, GXL WIRE
4. CRIMP: MUST MEET SAE/J559-21 STANDARD
5. RATING: MAX. 25A, 32Vdc
6. MAX TEMPERATURE 105°C
7. DATE CODE AND MOLD CAVITY NUMBER MARKED ON ALL UNITS.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES			
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.			
⊙	DENOTES CRITICAL CHARACTERISTICS.		
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE		
⬢ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		
COPIES TO		MATL SPEC	
1 9 18		SEE NOTES	
2 10 19		FINISH	
3 12 20		SEE NOTES	
4 13 21		DRW DHM	DATE 11/21/07
5 14 23		SCALE	1:1
6 15 33		CHK	DATE
7 16 43		SUPER DR	
8 17 53		APPD	DATE
		FINSH GOOD WT	GRAMS/PIECE
TOLERANCE UNLESS OTHERWISE SPECIFIED ONE PLACE DEC +/- .3 THREE PLACE DEC +/- .100 TWO PLACE DEC +/- .25 ANGULAR +/- 1°			
3RD ANGLE PROJECTION		TITLE	
		ATO IN-LINE FUSEHOLDER	
Littelfuse DES PLAINES, ILLINOIS 60016		REVISION	DRWG. NO. OUTLINE SERIES
		B	FHAC0003ZXJ

METRIC

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED