

# SPECIFICATIONS:

**VOLTAGE RATING:** 600Vac/dc

**AMP RATING:** 30A


**INTERRUPT RATING:** 200kA


**WIRE RANGE:** 0.75-10mm<sup>2</sup>  
18-4 AWG

**SUGGESTED TORQUE:** (1) 0.75-25mm<sup>2</sup> 2.0-2.5 Nm  
18-8 AWG 18-22 lb-in  
(2) 0.75-10mm<sup>2</sup> 2.0-2.5 Nm  
18-6 AWG 18-22 lb-in  
(1) 6-4 AWG 22-26 lb-in

**APPROVALS:** UL Listed (E14721)  
CSA Certified

REVISION				
REV	DATE	DESCRIPTION		
A	10/3/22	525710GCP - RELEASE MRY		

1				
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE			
●	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
Ⓢ	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.			
MATL SPEC		FINISH		
DRW JMOLER	DATE 9/23/2022	SCALE NTS	FINISH GOOD WT GRAMS/PIECE	
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994				
3RD ANGLE PROJECTION 				
TITLE LFPSC001 OUTLINE				

 <b>Littelfuse®</b> CHICAGO, ILLINOIS 60631	REVISION A	DRWG NO. OL-LFPSC001	SHEET 1 OF 1
-------------------------------------------------------------------------------------------------------------------------------------	---------------	-------------------------	--------------