







PART NUMBER	"A"	"B"	"C"	"D"	LEAD "A" COLOR	LEAD "B" COLOR	LEAD "A" SIZE	LEAD "B" SIZE	LEAD "A" STRIP	LEAD "B" STRIP	INSULATION TYPE	LTR	DATE	REVISION	CHK	APD
0FHM0003ZXJU	305±5 [12.01±0.2]	305±5 [12.01±0.2]	12.7±2 [0.50±0.08]	12.7±2 [0.50±0.08]	ORANGE	ORANGE	16 AWG	16 AWG	PARTIAL	PARTIAL	GXL	A	25/Nov/16	516790GCC - NEW RELEASE	FYUE	



- NOTES:
- HOLDER MATERIAL: BLACK TPV
 - CONTACTS: C194 COPPER ALLOY: TIN-PLATED
 - WIRE: STRANDED COPPER, 125°C RATED, 16AWG GXL WIRE
 - CRIMP: MUST MEET SAE/USCAR 21 STANDARD
 - FUSE RATING: MAX 20A, 32Vdc
 - FUSEHOLDERS SHOULD NOT BE PLACED UNDER TENSION IN FINAL APPLICATION
 - MAX TEMPERATURE 125°C

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES			
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.			
⊙	DENOTES CRITICAL CHARACTERISTICS.		
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE		
⬢ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		
COPIES TO		MATL SPEC	
1 9 18		SEE NOTES	
2 10 19		FINISH	
3 12 20		SEE NOTES	
4 13 21	DRW	FYUE	DATE 25/Nov/16
5 14 23	CHK	DATE	SCALE 1:1
6 15 33	APPD	DATE	SUPER DR
7 16 43			FINSH GOOD WT
8 17 53			GRAMS/PIECE
TOLERANCE UNLESS OTHERWISE SPECIFIED ONE PLACE DEC +/- .3 THREE PLACE DEC +/- .100 TWO PLACE DEC +/- .15 ANGULAR +/- 1°			
3RD ANGLE PROJECTION	TITLE		
	INLINE MINI HOLDER-16AWG ORANGE		
Littelfuse		REVISION	DRWG. NO.
DES PLAINES, ILLINOIS 60016		A	OL-0FHM0003ZXJU
			OUTLINE

METRIC

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED