


4

3

2

1



NOTES:

1. SILVER CONTACT SURFACES
2. ALL STEEL PARTS PLATED
3. ALL DIMENSIONS REF. ONLY
4. PARTS MAY BE ASSEMBLED OR SUPPLIED IN A BAG
5. RATING:
CONTINUOUS - 175 AMPS 6-12-24-36 V DC
INTERMITTENT-1000 AMPS MAX 6-12-24-36 V DC 15 SECONDS 'ON' 5 MINUTES 'OFF'
6. TORQUE SPECIFICATIONS:
MOUNTING STEM NUTS: 20 FT LBS [27 N.m] MAX
3/8" NUTS 70-90 IN LBS [8-10 N.m]

①

Revision Control Record				Rev.	Description of Change	ECN No.	Date	Tolerances Unless otherwise specifically noted, the following are default tolerances:			PROPRIETARY INFORMATION		Special Characteristics:		Cole Hersee Co.	
Rev.	Description of Change	ECN No.	Date					2-places +/- 0.02"	3-places +/- 0.005"	Angular +/- 1°	This Engineering Drawing, and the information contained herein, is proprietary to Cole Hersee Company and may not be disclosed, re-produced, or in any other way transferred or communicated to any other party without the express written consent of an authorized representative of Cole Hersee Company.		Critical Characteristic, relating to Safety and/or Regulatory Compliance		20 Old Colony Ave., South Boston, MA, 02127 Phn: 617-268-2100 Web: www.colehersee.com	
AA	REVISED NOTES	08680	11/24/08								Metric: Shown in [] refers to equivalent English Dim Tol		Significant Characteristic relating to Process Control		Description: SWITCH, MASTER DISCONNECT	
											"REF." or an Asterisk (*) = Non-Toleranced Reference Dimension, shown for clarification purposes only.		Control Dimension relating to Form - Fit - Function as defined by Cole Hersee Company and/or the Customer		Drawing / Part No.: 2484-A	
											NOTE: All tolerances are Non-Cumulative.		KC		Current Rev. AA	
											FORM CHT-6 (2/07)		Used On or Ref.:		Scale: 1:1	
											Drawn BY: PJS		Date Drawn: 12/27/55		Pg. 1 of 1	

4

3

2

1