



- NOTES:
1. MATERIAL: COPPER C1100, TIN PLATED
 2. UNLESS OTHERWISE NOTED, BURR SHALL NOT EXCEED 10% OF THE RAW MATERIAL THICKNESS AT ANY LOCATION
 3. PART TO BE CLEAN, DEGREASED, FREE OF CONTAMINATION



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES											
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.											
		DENOTES CRITICAL CHARACTERISTICS.									
CPK		DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE									
		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS									
CP		DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE									
		NO	COMPONENT NO		DESCRIPTION				QTY/M		U/M
BILL OF MATERIAL											

COPIES TO		MATL SPEC		SEE NOTE	
1	9 18	TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)		FINISH	
2	10 19			SEE NOTE	
3	12 20				
4	13 21			SCALE	
5	14 23			DATE 06/26/13	
6	15 33			DATE	
7	16 43			DATE	
8	17 53			DATE	
		GRAMS/PIECE		FINISH GOOD WT	
DIMENSION		0.5 - 3	UP TO OVER	UP TO OVER	UP TO OVER
TOLERANCE		+0.05	+0.05	+0.1	+0.15
3RD ANGLE PROJECTION					
		TITLE 4 POSITION BUS BAR			
		- FLEX MIDI HOLDER			
		REVISION		DRWG. NO.	
		B		OL-882-267-004	
					
		CHICAGO, USA 773-628-1000			