



PART NUMBER	"A"	"B"	"C"	"D"	LEAD "A" COLOR	LEAD "B" COLOR	INSULATION TYPE
FHAC0002ZXJ	89.5±5 [3.524]	89.5±5 [3.524]	6.35±2 [0.25]	6.35±2 [0.25]	ORANGE	ORANGE	GXL
FHAC0002ZXJA	243.5±5 [9.587]	243.5±5 [9.587]	N/A	N/A	RED	RED	GXL
FHAC0002ZXJB	102.0±5 [4.016]	805.0±5 [31.693]	6.35±2 [0.25]	6.35±2 [0.25]	PURPLE	PURPLE	GXL
FHAC0002ZXJC	89.5±5 [3.524]	89.5±5 [3.524]	6.35±2 [0.25]	6.35±2 [0.25]	PURPLE	PURPLE	GXL
FHAC0002ZXJD	101.6±5 [4.000]	101.6±5 [4.000]	8.00±2 [0.315]	8.00±2 [0.315]	PURPLE	PURPLE	UL3266
FHAC0002ZXJE	305.0±5 [12.008]	102.0±5 [4.016]	10.00±2 [0.394]	10.00±2 [0.394]	RED	RED	GXL

LTR	DATE	REVISION	CHK	APD
A	06/20/07	63273 - RELEASED DHM		
B	11/21/07	000218ER-RELEASED FHAC0002ZXJA DHM		
C	10/28/09	000822ER-RELEASED FHAC0002ZXJB & FHAC0002ZXJC GMB		
D	05/27/13	508356ERA-RELEASED FHAC0002ZXJD FYUE		
E	12/11/14	511356ERA-RELEASED FHAC0002ZXJE FYUE		



- NOTES:
1. HOLDER MATERIAL: BLACK RUBBER
 2. CONTACTS: COPPER ALLOY, TIN-PLATED
 3. WIRE: 12 AWG STRANDED COPPER, 125°C RATED
 4. CRIMP: MUST MEET SAE/USCAR 21 STANDARD
 5. RATING: MAX. 30A, 32V_{ac}
 6. MAX. TEMPERATURE 125°C
 7. FUSEHOLDER SHOULD NOT BE PLACED UNDER TENSION IN FINAL APPLICATION.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES			
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.			
	DENOTES CRITICAL CHARACTERISTICS.		
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE		
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		
COPIES TO		MATL SPEC	
		SEE NOTES	
1 9 18	FINISH		
2 10 19	SEE NOTES		
3 12 20			
4 13 21	DRW DHM	DATE 06/20/07	SCALE 1:1
5 14 23	CHK	DATE	SUPER DR
6 15 33	APPD	DATE	FINISH GOOD WT
7 16 43	GRAMS/PIECE		
8 17 53			
TOLERANCE UNLESS OTHERWISE SPECIFIED			
ONE PLACE DEC +/- .3		THREE PLACE DEC +/- .100	
TWO PLACE DEC +/- .25		ANGULAR +/- 1°	
3RD ANGLE PROJECTION 	TITLE ATO IN-LINE FUSEHOLDER		
 DES PLAINES, ILLINOIS 60016		REVISION E	DRWG. NO. OUTLINE OL-FHAC0002ZXJ

METRIC

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED