

EX-14874

Diagram illustrating the assembly components and dimensions:

- HEX NUT
- BUSHING 7/16-20
- SHAFT
- LOCKWASHER
- TERMINAL INSULATOR
- TERMINAL (4 REQ'D)
- 21.33 REF (Height dimension)
- 40.89 REF (Width dimension)

Technical drawing of a normally open solenoid valve. The drawing includes a top view on the left and a side view on the right. Dimensions are given in inches.

Top View Dimensions:

- Overall width: 14.22 REF
- Overall height: 15.87 REF
- Inner circular feature diameter: 8.509 / 8.610

Side View Dimensions:

- Overall height: 28.95 REF
- Top mounting bracket width: 7.62 REF
- Coil assembly height: 9.65 REF
- Coil assembly width: 2.28 REF
- Valve body width: 11.17 REF
- Valve body depth: 1.52 REF

Label: NORMALLY "ON"

METRIC

NORMALLY "ON" → → →
BREAKS CONTACT AT BOTH CIRCUITS (1 TO 3 & 2 TO 4)
AFTER DEPRESSING PLUNGER 3 175 ± 762 AND CONTACT
REMAINS BROKEN THRU THE REMAINDER OF FULL TRAVEL

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'D	SCALE	DATE DRAWN
								<i>✗</i>	EA	<i>74</i>		11	6-28-61
								FINISH <i>✗</i>	 Cole Hersee Co. 0 DCO ON VENUE SOU' BOSTON M S 02				DATE BLUEPRINT
								TOLERANCES	SWITCH, MOMENTARY, DPST				91801
								DECIMAL ± METRIC ±					
				E	REDRAWN	6-28-61	AK						

CH 188(4 78)