





PART NO.
GDB61601Z



- NOTES:
1. AGENCY INFORMATION:
UL FILE NO. E309688
 2. MATERIALS:
INSULATOR-THERMOPLASTIC
CONNECTOR-BRASS
 3. TERMINATION:
LINE: 8AWG-2/0
LOAD: 4-14 AWG
 4. RATINGS:
600V
MAXIMUM AMP PER POLE-160A
 5. TORQUE:
LINE: 35.5 IN-LB
LOAD: 17.5 IN-LB

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

● DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS,-MINIMUM CPK VALUE

ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.

CP DENOTES CP DIMENSIONS,-MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

CP										MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.										BILL OF MATERIAL															
																				COPIES TO		MATL SPEC		FINISH		NONE									
																				1	9	18	DRW	M	YORK	DATE	4/9/18	SCALE							
																				2	10	19													
																				3	12	20	CHK		DATE		SUPER DRW								
																				4	13	21			DATE										
																				5	14	23	APPD		DATE		RAW STK WT								
																				6	15	33					LBS/M								
																				7	16	43													
																				8	17	53													
																				TITLE															
																				GDB6160 SERIES DISTRIBUTION BLOCK OUTLINE															
																				LTR		REVISION										CHK		APD	
																				A		519180GCP - RELEASE 4/17/18 MRY													