



THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.





NOTES: (UNLESS OTHERWISE SPECIFIED)
1. DESCRIPTION:
1.1. ASSOCIATED 3D CAD FILE DEFINES ALL NON-DIMENSIONED FEATURES.

2. MATERIAL:
2.1. MATERIAL SHALL BE PA66+GF30% FOR PLASTIC COMPONENT AND COPPER C2100 FULL HARD WITH COATING FOR METAL COMPONENT .

3. THE MAX CONTINOUS CURRENT WHICH CAN CARRY IS 30A.



SECTION A-A



REVISIONS



ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PER EC # 520273 : INITIAL RELEASE	12/19/2018	D.CHENG

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.

●	DENOTES PRODUCTS CRITICAL CHARACTERISTICS
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENDAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF.ISO2768-M)

DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120	120 - 400	ANGLE
TOLERANCES	±0.1	±0.1	±0.2	±0.3	±0.5	±0.5°

		NAME	DATE	<div> Exercise Applied Answer's Delivered No.6 Xinghai Street,Suzhou Industry Park,China Phone +86 512 6761 3189 Fax +86 512 6761 1489</div>	
DRAWN	D CHENG	29/6/2015	<div>TITLE</div> <div>MCASE Terminal Adapter</div>		
CHECKED	-	-			
	-	-			
	-	-			
	-	-			
THIRD ANGLE PROJECTION			<div>SIZE</div> <div>B</div> <div>DWG. NO.</div> <div>OL-875-584</div> <div>REV.</div> <div>A</div>		
<div></div>					
DO NOT SCALE DRAWING			SCALE 2:1		SHEET 1 OF 1