






THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO #5300036. INITIAL RELEASE. DSILVA	3/7/2022	L.ARGIL



- NOTES:
- 1/2" DRAFT MAX PER SIDE UNLESS NOTED
 - MATERIAL: PET, GREY COLOR.

NO.	COMPONENT NO.	COMPONENT NAME	QTY	U		
TOLERANCE UNLESS OTHERWISE SPECIFIED						
TWO PLACE DEC ±0.01	THREE PLACE DEC ±0.005	FRACTION ±	ANGULAR ±1°			
DIMENSIONS ARE SHOWN IN INCHES. UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.						
PER CHNPD20-008 PROCEDURE	●	FIT/ FUNCTION CRITICAL CHARACTERISTICS				
	<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL				
	CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE				
	(ST)	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS				
	CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE				
		NAME	DATE			
DRAWN	D. SILVA		1/17/2022			
CHECKED	-		-			
	-		-			
	-		-			
FORM NO. CVP-PE40-0005 REV B		 Expertise Applied Answers Delivered TITLE 80A MAXI SPLASHPROOF W/O TABS				
THIRD ANGLE PROJECTION						
		SIZE C	DWG. NO. OUTLINE	REV. A		
DO NOT SCALE DRAWING		SCALE 2:1	SHEET 1 OF 1			