






P1 P2 P3 P4 P5 P6 P7

PART NAME	BLANK_1 SEALS	#10 CABLE SEALS	#16/1 CABLE SEALS	BLANK_2 SEALS	#16/2 CABLE SEALS	#25 CABLE SEALS	#35 CABLE SEALS	#50 CABLE SEALS
PART NUMBER	868-951	868-952	868-953	868-954	868-955	868-956	868-957	868-958
CABLE SEALS								
APPLICATION POSITION	P1,P7	P1,P7	P1,P7	P2,P3,P5,P6	P2,P3,P5,P6	P2,P3,P5,P6	P2,P3,P5,P6	P4
CABLE SECTION ISO_6722	N/A	10mm2	10mm2	N/A	16mm2	25mm2	35mm2	50mm2

NOTE:
SEALS NOT INCLUDED WITH THIS PART
FOR REFERENCE ONLY, MUST BE ORDERED SEPERATELY



NO	DESCRIPTION	QTY/M	U/M
6	BREATH VENT	1	
5	BIG BASE	1	
4	BUSS BAR	1	
3	COVER_GASKET	1	
2	TETHER	1	
1	COVER	1	

BILL OF MATERIAL																								
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES																								
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.																								
	DENOTES CRITICAL CHARACTERISTICS.																							
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE																							
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS																							
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE																							
COPIES TO	MATL SPEC SEE SHEET 1																							
1 9 18	<table><tr><td colspan="2">FINISH</td></tr><tr><td>DRW</td><td>FYUE</td><td>DATE</td><td>06/26/14</td><td>SCALE</td><td>1:1</td></tr><tr><td>CHK</td><td></td><td>DATE</td><td></td><td>SUPER DR</td><td></td></tr><tr><td>APPD</td><td></td><td>DATE</td><td></td><td>FINSH GOOD WT</td><td></td></tr></table>				FINISH		DRW	FYUE	DATE	06/26/14	SCALE	1:1	CHK		DATE		SUPER DR		APPD		DATE		FINSH GOOD WT	
FINISH																								
DRW					FYUE	DATE	06/26/14	SCALE	1:1															
CHK						DATE		SUPER DR																
APPD						DATE		FINSH GOOD WT																
2 10 19																								
3 12 20																								
4 13 21																								
5 14 23																								
6 15 33																								
7 16 43																								
8 17 53																								
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-MH)																								
DIMENSION	UP TO 0.5 - 3	OVER 3 - 6	UP TO 6 - 30	OVER 30 - 120	UP TO 120 - 400																			
TOLERANCE																								
3RD ANGLE PROJECTION	TITLE																							
	LTX Power Distribution Module																							
		REVISION	DRWG. NO.																					
DES PLAINES, ILLINOIS 60016		A	OL-07981002ZXS																					
					2 OF 2																			

METRIC
ASSEMBLY

Littelfuse
DES PLAINES, ILLINOIS 60016

2 OF 2

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED