


REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	GCF#524592 INITIAL RELEASE	SEP./25/2021	D. ZHANG



CIRCUIT SCHEMATIC DIAGRAM








TABLE 1: TECHNICAL PARAMETERS

ITEM		PARAMETER		
		DCNLM200NB12-01	DCNLM200NB24-01	DCNLM200NB48-01
RATED COIL VOLTAGE		12V DC	24V DC	48V DC
HOLD POWER	START POWER	MAX 180W		
	MAINTAIN POWER	MAX 9W		
OPERATING VOLTAGE IN COLD STATE AT (20±5)°C	PICKUP	MAX 8.4V DC	MAX 16.8V DC	MAX 33.6V DC
	RELEASE	MIN 1V DC	MIN 2V DC	MIN 4V DC
OPERATE TIME		MAX 50ms		
RELEASE TIME		MAX 20ms		
BOUNCE TIME		MAX 7ms		
RATED CONTACT VOLTAGE		48V DC		
MAXIMUM CONTACT VOLTAGE		60V DC		
RATED CONTACT CURRENT		200A		
CONTACT VOLTAGE DROP		≤50mV@100 A		
LIMIT BREAKING ABILITY		4le/5ms,1CYCLES		
DIELECTRIC STRENGTH		1000V AC, 50Hz,1min., LEAKAGE CURRENT ≤1 mA		
INSULATION RESISTANCE		≥50MΩ@500VDC		
ELECTRIC LIFE		6000 CYCLES		
MECHANICAL LIFE		100,000 CYCLES		
WORKING DUTY		CONTINUOUS		

NOTES:

- ALL SIZES ARE FOR REFERENCE ONLY.
- MATERIALS AND FINISHING:
 - BASE: THERMOSETTING PLASTIC, UL94V-0.
 - CONTACTS: SILVER ALLOY.
 - COIL STUD: COPPER ALLY, SILVER PLATED.
- PRODUCT TECHNICAL PARAMETERS: SEE TABLE 1.
- PRODUCT AND NAMEPLATE(THE CHARACTER CONTENT AT "A" AND "B") CONFIGURATION SEE TABLE 2.
- CONTACT ARRANGEMENT: SPST-NO.
- CONNECTION STUD: M8 STUD, RECOMMENDED TORQUE 9 N•m ~ 11 N•m; M4 STUD, RECOMMENDED TORQUE 1.7 N•m ~ 2.5 N•m.
- MOUNTING: M5 BOLT, RECOMMENDED TORQUE 4 N•m ~ 5 N•m.

TABLE 2

PRODUCT PN		"A"	"B"
DCNLM200NB12-01		DCNLM200NB12-01	Rated Coil Voltage: 12VDC
DCNLM200NB24-01		DCNLM200NB24-01	Rated Coil Voltage: 24VDC
DCNLM200NB48-01		DCNLM200NB48-01	Rated Coil Voltage: 48VDC
DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.			
PER CHNFPD20-008 PROCEDURE	● FIT/ FUNCTION CRITICAL CHARACTERISTICS		
	<S> SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL		
	CPK DENOTES CPK DIMENSIONS MINIMUM CPK VALUE		
	(ST) DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
	CP DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		
NAME		DATE	
DRAWN	MJ. DAI	SEP./25/2021	
CHECKED	J. LI	SEP./30/2021	
	-	-	
	-	-	
FORM NO.: CVP-PE40-0005 REV B		Littelfuse Expertise Applied Answers Delivered	
THIRD ANGLE PROJECTION			
TITLE		DCNL 200A 48V CONTACTOR	
		SIZE C	DWG. NO. OUTLINE
DO NOT SCALE DRAWING		OL-DCNLM200NB.CHT2	
SCALE 1:1		REV. A	
		SHEET 1 OF 1	



DCNLM200NB, CHT2