

Ø25.4 ± 0.38
[Ø1.000 ± 0.015]

3.2 ± 0.15
[0.125 ± 0.006]

8.7 ± 0.25
[0.344 ± 0.010]

68.26 ± 1.59
[2.688 ± 0.063]

76.24 ± 1.59
[3.002 ± 0.063]

91.8 ± 1.59
[3.615 ± 0.063]

54.0 ± 1.00
[2.125 ± 0.039]

17.0 ± 0.89
[0.670 ± 0.035]

REVISION

REV	DATE	DESCRIPTION
A	7/6/23	526696GCP - RELEASE MRY

1				
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M


BILL OF MATERIAL

<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE
●	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

A

MATL SPEC		FINISH	
DRW JMoler	DATE 6/22/2023	SCALE NTS	FINISH GOOD WT GRAMS/PIECE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994



TITLE L50S 70-100A OUTLINE



REVISION	DRWG NO.	SHEET 1 OF 1
A	OL-L50S100	