

| PART NUMBER | FIGURE | "A"         | "B"       | "C"      | "D"      | LEAD "A" COLOR | LEAD "B" COLOR | INSULATION TYPE | WIRE SIZE | RATING MARK | PKG QTY |
|-------------|--------|-------------|-----------|----------|----------|----------------|----------------|-----------------|-----------|-------------|---------|
| FHJC1001G   | 1      | 102.0±5.0   | 102.0±5.0 | 9.0±2.0  | 9.0±2.0  | RED            | RED            | GXL (STANDARD)  | 10 AWG    | 40A         | 250     |
| FHJC1001GB  | 1      | 102.0±5.0   | 102.0±5.0 | 9.0±2.0  | 9.0±2.0  | RED            | RED            | TXL (STANDARD)  | 10 AWG    | 40A         | 250     |
| FHJC1001FXA | 1      | 280.0±5.0   | 400.0±5.0 | 9.0±2.0  | 9.0±2.0  | RED            | RED            | GXL (STANDARD)  | 10 AWG    | 40A         | 200     |
| FHJC1001HC  | 1      | 1070.0±5.0  | 132.0±5.0 | 7.0±2.0  | 13.0±2.0 | RED            | RED            | GXL (STANDARD)  | 10 AWG    | 40A         | 100     |
| FHJC1002G   | 1      | 102.0±5.0   | 102.0±5.0 | 9.0±2.0  | 9.0±2.0  | RED            | RED            | GXL (STANDARD)  | 8 AWG     | 60A         | 250     |
| FHJC1002GA  | 1      | 1050.0±10.0 | 235.0±5.0 | 9.0±2.0  | 9.0±2.0  | RED            | RED            | GXL (STANDARD)  | 8 AWG     | 60A         | 100     |
| FHJC1002GB  | 1      | 1150.0±10.0 | 850.0±5.0 | 9.0±2.0  | 9.0±2.0  | RED            | RED            | GXL (STANDARD)  | 8 AWG     | 60A         | 50      |
| FHJC1002GC  | 1      | 400.0±5.0   | 400.0±5.0 | 9.0±2.0  | 9.0±2.0  | RED            | RED            | GXL (STANDARD)  | 8 AWG     | 60A         | 50      |
| FHJC1002GD  | 1      | 920.0±5.0   | 630.0±5.0 | 14.2±2.0 | 14.2±2.0 | RED            | RED            | GXL (STANDARD)  | 8 AWG     | 60A         | 50      |
| FHJC1002GE  | 1      | 1004.0±10.0 | 630.0±5.0 | 14.2±2.0 | 14.2±2.0 | RED            | RED            | GXL (STANDARD)  | 8 AWG     | 60A         | 50      |
| FHJC1002L   | 1      | 102.0±5.0   | 102.0±5.0 | 9.0±2.0  | 9.0±2.0  | RED            | RED            | GXL (STANDARD)  | 8 AWG     | 60A         | 50      |
| FHJC1002MB  | 1      | 247.0±5.0   | 247.0±5.0 | 9.0±2.0  | 9.0±2.0  | RED            | RED            | GXL (STANDARD)  | 8 AWG     | 60A         | 200     |
| FHJC2001G   | 2      | 102.0±5.0   | 102.0±5.0 | 9.0±2.0  | 9.0±2.0  | RED            | RED            | GXL (STANDARD)  | 10 AWG    | 40A         | 250     |
| FHJC2002G   | 2      | 102.0±5.0   | 102.0±5.0 | 9.0±2.0  | 9.0±2.0  | RED            | RED            | GXL (STANDARD)  | 8 AWG     | 60A         | 250     |
| FHJC2002L   | 2      | 102.0±5.0   | 102.0±5.0 | 9.0±2.0  | 9.0±2.0  | RED            | RED            | GXL (STANDARD)  | 8 AWG     | 60A         | 50      |

NOTES:  
1. HOLDER MATERIAL: BLACK TPV MATERIAL  
2. CONTACTS: TIN-PLATED COPPER ALLOY  
3. WIRE SIZE & LENGTH: SEE CHART  
4. MAX TEMPERATURE: 125°C  
5. RATING MARKING: SEE CHART  
6. FUSE HOLDERS SHOULD NOT BE PLACED UNDER TENSION IN FINAL APPLICATION.  
7. ALL PARTS PACKAGED BULK IN QTY SHOWN.

| LTR | DATE      | REVISION                                                                                                                                                                                                                                                                | CHK | APD |
|-----|-----------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----|-----|
| A   | 07/15/09  | 000735ER-RELEASE FHJC1002GA GMB                                                                                                                                                                                                                                         |     |     |
| B   | 12/16/09  | SA37-ADDED TOLERANCES TO DM1S. GMB                                                                                                                                                                                                                                      |     |     |
| C   | 01/25/11  | REMOVED MOUNTING HOLE THROUGH BODY (FIG 1.); COMPILED ALL FHJC HOLDERS ONTO ONE PRINT; ADDED PART # FHJC1001HC; UPDATED NOTES (CORRECTED MATERIALS, ADDED PKG QTY); ADDED BRACKET VERSION VIEWS; PRINT NAME CHANGED FROM OL-FHJC1000G TO OL-FHJC00000. ERN-501557ERA KH |     |     |
| D   | 04/30/15  | 511832GCA-RELEASE FHJC1002GB FYUE                                                                                                                                                                                                                                       |     |     |
| E   | 05/07/15  | 511833GCA-RELEASE FHJC1001GB FYUE                                                                                                                                                                                                                                       |     |     |
| F   | 07/06/15  | 514472GCA-CHANGE DIMENSIONS OF FHJC1002GB FYUE                                                                                                                                                                                                                          |     |     |
| G   | 20/Apr/16 | 515810GCA-RELEASE FHJC1002GD AND FHJC1002GE FYUE                                                                                                                                                                                                                        |     |     |
| H   | 02/Mar/17 | 517171ECC-CHANGE WIRE LENGTH 630 WAS 720 OF FHJC1002GD AND FHJC1002GE FYUE                                                                                                                                                                                              |     |     |




FIGURE 1. STANDARD HOLDER







FIGURE 2. HOLDER WITH MOUNTING BRACKET



METRIC  
ASSEMBLY

|                                                                                                     |                                                                                                                                                                                  |                                            |                                                                                       |              |           |                |
|-----------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------|---------------------------------------------------------------------------------------|--------------|-----------|----------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.<br>DIMENSIONS IN BRACKETS [ ] ARE INCHES |                                                                                                                                                                                  |                                            |                                                                                       |              |           |                |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.                                      |                                                                                                                                                                                  |                                            |                                                                                       |              |           |                |
|                | DENOTES CRITICAL CHARACTERISTICS.                                                                                                                                                |                                            |                                                                                       |              |           |                |
| CPK                                                                                                 | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE                                                                                                                                       |                                            |                                                                                       |              |           |                |
|                | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION<br>OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT<br>AND TRACKING TO BE DEFINED IN<br>LITTELFUSE INSPECTION INSTRUCTIONS |                                            |                                                                                       |              |           |                |
| CP                                                                                                  | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE<br>MUST BE WITHIN THE DIMENSIONAL LIMITATIONS<br>SHOWN ON DRAWING AND INITIALLY LOCATED TO<br>ALLOW FOR MAXIMUM TOOL LIFE               |                                            |  |              |           |                |
| COPIES TO                                                                                           |                                                                                                                                                                                  | MATL SPEC                                  |                                                                                       |              |           |                |
| 1 9 18                                                                                              | FINISH                                                                                                                                                                           |                                            |                                                                                       |              |           |                |
| 2 10 19                                                                                             |                                                                                                                                                                                  |                                            |                                                                                       |              |           |                |
| 3 12 20                                                                                             |                                                                                                                                                                                  |                                            |                                                                                       |              |           |                |
| 4 13 21                                                                                             | DRW                                                                                                                                                                              | GMB                                        | DATE 07/15/09 SCALE 1:1                                                               |              |           |                |
| 5 14 23                                                                                             | CHK                                                                                                                                                                              |                                            | DATE SUPER DR                                                                         |              |           |                |
| 6 15 33                                                                                             | APPD                                                                                                                                                                             |                                            | DATE FINSH GOOD WT                                                                    |              |           |                |
| 7 16 43                                                                                             |                                                                                                                                                                                  |                                            |                                                                                       |              |           |                |
| 8 17 53                                                                                             | GRAMS/PIECE                                                                                                                                                                      |                                            |                                                                                       |              |           |                |
| TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)                                            |                                                                                                                                                                                  |                                            |                                                                                       |              |           |                |
| DIMENSION                                                                                           | 0.5 - 3                                                                                                                                                                          | OVER 3 - 6                                 | OVER 6 - 30                                                                           | UP TO 30     | UP TO 120 | OVER 120 - 400 |
| TOLERANCE                                                                                           | ±0.1                                                                                                                                                                             | ±0.1                                       | ±0.2                                                                                  | ±0.3         | ±0.5      |                |
| 3RD ANGLE<br>PROJECTION                                                                             |                                                                                                                                                                                  | TITLE                                      |                                                                                       |              |           |                |
|                |                                                                                                                                                                                  | INLINE JCASE HOLDER<br>WITH STANDARD COVER |                                                                                       |              |           |                |
|                |                                                                                                                                                                                  | REVISION                                   |                                                                                       | DRWG. NO.    |           | OUTLINE        |
| DES PLAINES, ILLINOIS 60016                                                                         |                                                                                                                                                                                  | H                                          |                                                                                       | OL-FHJC00000 |           | SERIES         |

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED