






REV.		DESCRIPTION	DATE	DESIGNED	APPROVED
A		FIRST ISSUE OF OUTLINE DRAWING	08-July-2020	Gasparini	Tinto



#### ELECTRICAL CHARACTERISTICS

- Nominal operating voltage: 12 ÷ 24 V
- Max continuous current on main contacts: 250 A
- Max current on main contacts short duration: 2000 A for 30 sec.

#### MECHANICAL CHARACTERISTICS



- Number of electrical and mechanical operations: 100.000
- Max locking torque nuts M12: 22 ± 1 Nm
- Max locking torque nuts M5: 1.6 ± 0.4 Nm

#### PRESCRIPTIONS

- (\*): Data of production
- We suggests to fix the device to the structure by screws M8 UNI 5931:1984 and plane washers 8.4 x 17 UNI 6592:1969 under head

SAP drawing number:

Material and treatments:

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.						
linear dimensions						
0,5	>3	>6	>30	>120	>400	>1000
3	6	30	120	400	1000	2000
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3
angle (for range of lengths)						
up to 10	>10	>50	>120	>400	>1000	>2000
±1°30'	±1°	±0°30'	±0°15'	±0°15'	±0°15'	±0°15'
●	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL					
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL					
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE					
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS					
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE					
NAME		DATE		<div> <b>Littelfuse</b></div> <div>Expertise Applied  Answers Delivered</div>		
DRAWN		L. Dal Molin				
CHECKED		-				
-		-				
-		-				
FORM NO. CVP-PE40-0013 REV A		TITLE		GENERAL ELECTRICAL MAIN SWITCH		
FIRST ANGLE PROJECTION		TGC/RMSM 24V SEP(+0-)		OL-08097262		
		SIZE: A2		DWG. NO.		OUTLINE REV. A
DO NOT SCALE DRAWING		SCALE 1:1		SHEET 1 OF 1		