






●TABLE 2 OPERATING VOLTAGE PARAMETER			
NO.	PN	NAME PLATE	
		"A" OF NAME PLATE	"B" OF NAME PLATE
1	DCNLB400NB24	DCNLB400NB24	24V DC
2	DCNLB400NB48	DCNLB400NB48	48V DC

Littelfuse
DCN1LB400NBXX
 Rated Oper. Voltage: 48VDC
 Rated Current: 400A
 Rated Coll Voltage: 300VDC
MADE IN CHINA

Pin 1 is connected to the positive terminal (+) of the input voltage source.
 Pin 2 is connected to the negative terminal (-) of the input voltage source.

Labels with arrows pointing to the component:
 "A" (SEE TABLE 2) points to the component body.
 "B" (SEE TABLE 2) points to the component body.



2 1