




ARTIKELNUMMER ARTICLE-No.	B1 IN mm	B2 IN mm	H1 IN mm	H2 IN mm	mm2
178.6116.100_	3.0	4.2	2.8	3.9	0.5 - 1
178.6116.2501/2	3.5	5.1	3.85	4.9	1.5 - 2.5
178.6116.2508	4.1	5.3	3.8	5.3	1.5 - 2.5
178.6116.400_	5.1	6.9	4.7	6.7	2.5 - 4
178.6116.600_	6.2	8.1	5.7	7.3	4 - 6

TOLERANZ DER TABELLENMAßE $\pm 0.2 \text{ mm}$.
CHART TOLERANCES $\pm 0.2 \text{ mm}$.

ALLGEMEINTOLERANZEN
GENERAL TOLERANCES
DIN ISO 2768-m



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

© DENOTES CRITICAL CHARACTERISTICS.

CPK

ST
DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION
OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT
AND TRACKING TO BE DEFINED IN
LITTELFUSE INSPECTION INSTRUCTIONS

CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

METRIC COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

BILL OF MATERIAL

	A	LTR	COPIES TO	MATL SPEC	CuFeAg
			1 9 18 2 10 19 3 12 20 4 13 21 5 14 23 6 15 33 7 16 43 8 17 53	FINISH	-
				DRW OPL	DATE 09/19/12
				CHK	DATE
				APPD	DATE
				TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-MH)	
			DIMENSION	0.5 - 3	UP TO OVER UP TO OVER UP TO OVER
			TOLERANCE	±0.05	±0.05 ±0.1 ±0.15 ±0.2

DFK-KONTAKT
DFK-CONTACT

CHK	APD	 CHICAGO, USA 773-628-1000	REVISION A	DRWG. NO. 178.6116.1000	OUTLINE
-----	-----	--	---------------	----------------------------	---------