


| ARTIKELNUMMER ARTICLE-No. | B1 IN mm | B2 IN mm | H1 IN mm | H2 IN mm | mm2 |
|------------------------------|----------|----------|----------|----------|-----------|
| 178.6116.100_ | 3.0 | 4.2 | 2.8 | 3.9 | 0.5 - 1 |
| 178.6116.2501/2 | 3.5 | 5.1 | 3.85 | 4.9 | 1.5 - 2.5 |
| 178.6116.2508 | 4.1 | 5.3 | 3.8 | 5.3 | 1.5 - 2.5 |
| 178.6116.400_ | 5.1 | 6.9 | 4.7 | 6.7 | 2.5 - 4 |
| 178.6116.600_ | 6.2 | 8.1 | 5.7 | 7.3 | 4 - 6 |

TOLERANZ DER TABELLENMABE ±0.2 mm.
CHART TOLERANCES ±0.2 mm.

ALLGEMEINTOLERANZEN
GENERAL TOLERANCES
DIN ISO 2768-m



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

© DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE

ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS

CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

METRIC
COMPONENT

| NO | COMPONENT NO | DESCRIPTION | QTY/M | U/M |
|------------------|--------------|-------------|-------|-----|
| BILL OF MATERIAL | | | | |

| LTR | DATE | REVISION | CHK | APD |
|-----|----------|---|-----|-----|
| A | 09/19/12 | 5061888A-REDRAW IN UG AND CHANGE TERMINAL SHAPE FROM ORIGINAL DRAWING OPL | | |

| | | |
|-----------|-----------|---------------------|
| COPIES TO | MATL SPEC | CuFeAg |
| 1 9 | FINISH | - |
| 2 10 | DRW OPL | DATE 09/19/12 |
| 3 12 | CHK | DATE SUPER DR |
| 4 13 | APPD | DATE FINISH GOOD WT |
| 5 14 | | GRAMS/PIECE |
| 6 15 | | |
| 7 16 | | |
| 8 17 | | |
| 18 | | |
| 19 | | |
| 20 | | |
| 21 | | |
| 22 | | |
| 23 | | |
| 33 | | |
| 43 | | |
| 53 | | |

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)

| | | | | | | |
|-----------|-----------|---------|---------|----------|-----------|-----------|
| DIMENSION | UP TO 0.5 | UP TO 3 | UP TO 6 | UP TO 30 | UP TO 120 | UP TO 400 |
| TOLERANCE | ±0.05 | ±0.05 | ±0.1 | ±0.15 | ±0.2 | ±0.2 |

3RD ANGLE PROJECTION

TITLE DFK-KONTAKT
DFK-CONTACT

REVISION DRWG. NO. A 178.6116.1000

Littelfuse
CHICAGO, USA 773-628-1000