






THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.



REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	GCF#524667 INITIAL RELEASE	AUG./25/2021	D. ZHANG
B8	B	ECR#525202 DELETE: "AUXILIARY CONTACT RESISTANCE" IN TABLE 1	5/10/2022	D. ZHANG



ITEM		PARAMETER					
		DCNHR100PF12	DCNHR100PF24	DCNHR100PF48	DCNH50PF12	DCNHR50PF24	DCNHR50PF48
RATED COIL VOLTAGE		12V DC	24V DC	48V DC	12V DC	24V DC	48V DC
OPERATING VOLTAGE IN COLD STATE AT (20±5) °C	PICK-UP (V DC)	MAX 8.4	MAX 16.8	MAX 33.6	MAX 8.4	MAX 16.8	MAX 33.6
	RELEASE(V DC)	MIN 1	MIN 2	MIN 4	MIN 1	MIN 2	MIN 4
PICK-UP TIME		MAX 25ms					
RELEASE TIME		MAX 12ms					
BOUNCE TIME		MAX 7ms					
MAIN CONTACT RESISTANCE (@ 20A)		MAX 2mΩ					
DIELECTRIC STRENGTH (LEAKAGE CURRENT ≤1 mA)		2200V AC, 50Hz,1min.					
INSULATION RESISTANCE		≥100MΩ@500VDC					
MAXIMUM CONTACT VOLTAGE		900V DC					
RATED CONTACT CURRENT		100A	100A	100A	50A	50A	50A
LIMIT BREAKING ABILITY		4le/5ms,1CYCLES					
ELECTRIC LIFE		3000 CYCLES(100A@450V DC)			6000 CYCLES(100A@450V DC)		
MECHANICAL LIFE		200,000 CYCLES					
WORKING DUTY		CONTINUOUS					

PRODUCT NUMBER	"A"	"B"	"C"
DCNHR100PF12	DCNHR100PF12	100A	12V DC
DCNHR100PF24	DCNHR100PF24	100A	24V DC
DCNHR100PF48	DCNHR100PF48	100A	48V DC
DCNHR50PF12	DCNHR50PF12	50A	12V DC
DCNHR50PF24	DCNHR50PF24	50A	24V DC
DCNHR50PF48	DCNHR50PF48	50A	48V DC

NOTES:

1. ALL SIZES ARE FOR REFERENCE ONLY.
2. MATERIALS AND FINISHED:
 - 2.1 HOUSING: THERMOSETTING PLASTIC, UL94V-0.
 - 2.2 CONTACTS: SILVER ALLOY.
3. PRODUCT PN AND NAMEPLATE CONFIGURATION RELATION SEE TABLE 2.
4. PRODUCT TECHNICAL PARAMETERS: SEE TABLE 1.
5. MAIN CONTACT ARRANGEMENT: SPST-NO.
6. CONNECTION BOLT: M5 BOLT, RECOMMENDED TORQUE 3 N·m ~ 4 N·m.
7. MOUNTING: M4 BOLT, RECOMMENDED TORQUE 1.7 N·m ~ 2.5 N·m.

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.																
PER CH-IND-2003 PROCEDURE	 FIT / FUNCTION CRITICAL CHARACTERISTICS															
	<S> SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL															
	CPK DENOTES CPK DIMENSIONS MINIMUM CPK VALUE															
	 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE AND PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS															
	CP DENOTES CP DIMENSIONS. MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE															
<table><tr><td>DRAWN</td><td>NAME</td><td>DATE</td></tr><tr><td></td><td>M.J. DAI</td><td>AUG./25/2021</td></tr><tr><td>CHECKED</td><td>J. LI</td><td>AUG./30/2021</td></tr><tr><td></td><td>-</td><td>-</td></tr><tr><td></td><td>-</td><td>-</td></tr></table>		DRAWN	NAME	DATE		M.J. DAI	AUG./25/2021	CHECKED	J. LI	AUG./30/2021		-	-		-	-
DRAWN	NAME	DATE														
	M.J. DAI	AUG./25/2021														
CHECKED	J. LI	AUG./30/2021														
	-	-														
	-	-														
FORM NO. CVP-P64-0005 REV B																
THIRD ANGLE PROJECTION																
																
TITLE																
DCNHR 100A HIGH VOLTAGE CONTACTOR WITH POLARITY																
 Littelfuse® Expertise Applied Answers Delivered																
DO NOT SCALE DRAWING	<table><tr><td>SIZE</td><td>DWG. NO.</td><td>REV.</td></tr><tr><td>C</td><td>OUTLINE</td><td>B</td></tr><tr><td colspan="2">OL-DCNHR100PF CHT</td><td></td></tr></table>	SIZE	DWG. NO.	REV.	C	OUTLINE	B	OL-DCNHR100PF CHT								
SIZE	DWG. NO.	REV.														
C	OUTLINE	B														
OL-DCNHR100PF CHT																
SCALE 1:1	SHEET 1 OF 1															