








Voltage (Max.)	32VDC	Mounting Screw	Blade Fuse Isometric View	
Input Terminal Rating	M5 Threaded Studs(100A Max)	4xM4xP0.7xL16		
Output Terminal Rating	30A Max. Per Circuit			
Connection Pad Option Available	Input Wire Size:#4-6 AWG			
	Output Wire Size:#12-16AWG		Blade Fuse Dim	
Fuse Specifications	For ATO Blade Fuses Only		 M4 Screws	ATO SERIELS
Torqure Rating for M5 Studs	2.25+0/-0.2Nm(20 in-lb)			
Torqure Rating for M4 Screws				
Mounting Torque Rating	0.9+0/-0.1Nm(8 in-lb)			
Temperature Rating	-25° C to +85°C			



REVERSIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	522970GCC NEW RELEASE DRAWING	04/MAR/2021	EDWARD.J
	B	523692 ECC ADD LASER MARKING	11/MAY/2021	EDWARD.J



- NOTES:
- MATERIALS:
BASE/HOUSING: BLACK PBT
COVER: TRANSPAREANCE PC
TERMINAL:TINNED COPPER
 - FUSES ASSEMBLY BY HANDS.
 - ALL FUSES MUST NOT EXCEED 70% OF RATED CURRENT

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.		
	FIT FUNCTION CRITICAL CHARACTERISTICS SYMBOL	
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL	
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE	
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS	
CP	DENOTES CP DIMENSIONS. MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE	
DIMENSION: MM TOLERANCES UNLESS OTHERWISE SPECIFIED ONE PLACE DECIMAL ± 0.5 THREE PLACES DECIMAL ± 0.100 TWO PLACES DECIMAL ± 0.20 ANGULAR ± 2°		
NAME	DATE	 Littelfuse® Expertise Applied Answers Delivered
Sunny Pan	22/OCT/2020	
Jason Li	22/OCT/2020	
-	-	
CHECKED		TITLE
FORM NO: CVP-PE40-0006 REV A		PDM 6 POS
THIRD ANGLE PROJECTION		
		SIZE C DWG. NO. OL-880027 REV. B
DO NOT SCALE DRAWING		
SCALE 1:1		SHEET 1 OF 1