





REV.		REVISIONS			
DESCRIPTION		DATE	GCF / ECR	DESIGNED	APPROVED
Initial Release		1-Feb-23		L.Dal Molin	M.Tinto



Tighten the connector nut with a torque of 7 ± 1 Nm

DOCUMENTO CORRELATO AL CERTIFICATO:
DOCUMENT CORRELATED TO THE CERTIFICATE:

SIRA 06 ATEX 2052X

Non sono ammesse modifiche senza l' approvazione della "Persona Autorizzata".
No modify is allowed without the "Authorized Person" approval.

CHARACTERISTICS

- Nominal operating voltage: 12V
- Working voltage: 13.5V
- Working voltage range: $7 \div 16$ V
- Max continuous current on contacts: 250A
- Max current short duration on contacts: 2000A for 30 sec.
- Number of mechanical and electrical cycles: 50.000
- Max torque of screws M10= 20 Nm
- We suggests to fix the Bms to the structure by screws M8 and plane washers under head
- (*) Data of production according to Littelfuse standard TSP00002 system D
- The distance between mobile contact and fixed contacts must be minimum 2 mm
- (\$) Components provided in the kit

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.								
linear dimensions								
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000		
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3		
angle (for range of lengths)								
up to 10	>10 50	>50 120	>120 400	>400 1000	>1000 2000	>2000 4000		
±1°30'	±1°	±0°30'	±0°15'	±0°15'	±0°15'	±0°15'		
● FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL								
<S> SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL								
CPK DENOTES CPK DIMENSIONS MINIMUM CPK VALUE								
ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS								
CP DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE								
NAME		DATE		 Littelfuse® Expertise Applied Answers Delivered				
DRAWN		L. Dal Molin					1 Feb 2023	
CHECKED		-					-	
-		-					-	
FORM NO: CVP-PE40-0013 REV A				TITLE BMS TGC/RMCDE-L 12V				
FIRST ANGLE PROJECTION								
				SIZE: A2 DWG. NO. OL-08097364 OUTLINE REV. A				
DO NOT SCALE DRAWING								
SCALE 1:2		SHEET 1 OF 1						