


CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED

PART No.	WIRE GA./ COLOR	"A"
0FNY0001ZXJ	#14 BLACK	203.2±5 (8.0)





DETAIL B



NOTES:
1. MAX FUSE RATING: 20A, 32VDC.
2. MAX. OPERATING TEMPERATURE: 80°C.
3. WIRE: COPPER STRANDED, UL 1015.
4. CONTACTS: C2680 ALLOY.
5. CRIMP: MUST MEET USCAR 21 STANDARD.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

CC — DENOTES CRITICAL CHARACTERISTICS.

CPK — DENOTES CPK DIMENSIONS,-MINIMUM CPK VALUE

ST — DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.

DENOTES CP DIMENSIONS,-MINIMUM CP VALUE (MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

UNCONTROLLED DOCUMENT

LTR	REVISION	CHK	APD
A	000490ER-RELEASED 9/05/08		

COPIES TO			
1	9	18	
2	10	19	
3	12	20	
4	13	21	
5	14	23	
6	15	33	
7	16	43	
8	17	53	

MATL SPEC
FINISH

DRW	DHM	DATE 09/05/08	SCALE 1=1
CHK		DATE	SUPER DRW
APPD		DATE	RAW STK WT LBS/M

TOLERANCE UNLESS OTHERWISE SPECIFIED
TWO PLACE DEC ±.01 FRACTION ±
THREE PLACE DEC ±.005 ANGULAR ±1°

TITLE: FUSEHOLDER, INLINE (WITH FUSE)

Littelfuse
DES PLAINES, ILLINOIS 60016

REVISION: A
DRWG. NO. 0FNY0001ZXJ
OUTLINE