




PART NUMBER	"A"	"B"	"C"	"D"	LEAD "A" COLOR	LEAD "B" COLOR	WIRE TYPE
OFHA0001ZXJ	101.6 +/- 5 (4.0)	101.6 +/- 5 (4.0)	6.35 +/- 2 (0.25)	6.35 +/- 2 (0.25)	BLACK	BLACK	16 AWG STRANDED COPPER 125C, GXL WIRE
OFHA0001ZXJA	177.8 +/- 5 (7.0)	177.8 +/- 5 (7.0)	6.35 +/- 2 (0.25)	6.35 +/- 2 (0.25)	RED	RED	16 AWG STRANDED COPPER 125C, GXL WIRE
OFHA0001ZXJB	101.6 +/- 5 (4.0)	101.6 +/- 5 (4.0)	13.0 +/- 2 (0.51)	13.0 +/- 2 (0.51)	BLACK	BLACK	16 AWG STRANDED COPPER 125C, GXL WIRE
OFHA0001ZXJD	101.6 +/- 5 (4.0)	101.6 +/- 5 (4.0)	NO STRIP	NO STRIP	BLACK	BLACK	16 AWG STRANDED COPPER 125C, GXL WIRE



- NOTES:
1. HOLDER MATERIAL : BLACK TPV.
 2. CONTACTS : COPPER ALLOY, TIN PLATED.
 3. WIRE : 16AWG STRANDED COPPER, 125 °C RATED, GXL WIRE
 4. CRIMP : MUST MEET SAE/USCAR 21 STANDARD.
 5. RATING : MAX. 20A, 32VDC.
 6. MAX. TEMP. : 105 °C.
 7. FUSEHOLDERS SHOULD NOT BE PLACED UNDER TENSION IN FINAL APPLICATION

METRIC
ASSEMBLY

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
⊙	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			

COPIES TO		MATL SPEC		REFER TO NOTES	
1	9	18	19	FINISH	
2	10	20	21	REFER TO NOTES	
3	12	22	23	DRW	SCALE 1:1
4	13	24	25	RLDJ	DATE 7/19/10
5	14	26	27	CHK	SUPER DR
6	15	28	29	DATE	
7	16	30	31	APPD	FINISH GOOD WT
8	17	32	33	DATE	GRAMS/PIECE
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-TH)				TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-TH)	
DIMENSION		0.5 - 3	UP TO OVER	3 - 6	UP TO OVER
TOLERANCE		+0.05	+0.05	+0.1	+0.15
3RD ANGLE PROJECTION		TITLE		AUTOFUSE HOLDER	
IN- LINE		IN- LINE		IN- LINE	
LITTLEFUSE		REVISION		DRWG. NO.	
LIPA CITY, BATANGAS, PHILIPPINES		D		OL-OFHA0001ZXJ	
OUTLINE		OUTLINE		OUTLINE	