



THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS

ZONE	REV.	DESCRIPTION	DATE	APPROVED
	C	ECN #07221: NOTES	6/21/07	
	D	ECN #08037: NOTES: BAGGED HARDWARE	1/16/08	
	E	ECO #521466: UPDATED NOTES, ADDED ITEM 1 AND 2 COLUMNS TO TABLE, UPDATED GEOMETRY	6/30/20	T.SURMA



46377-10 SHOWN




mm [inch]

(E) NOTES:

1. MATERIAL: BLACK THERMOPLASTIC
2. ACCEPTS ATC AND ATO TYPE FUSES AND PLUG-IN TYPE CIRCUIT BREAKERS
3. .250" x .032" QUICK CONNECT TERMINALS, TIN PLATED COPPER;
22.5A MAX PER CIRCUIT @12VDC;
FOR 24VDC APPLICATIONS, USE 24VDC RATED FUSES AND BREAKERS ONLY.
4. INPUT STUD #10-32:
100A MAX FOR INPUT STUD,
TORQUE, 2.25N-m (20 in-lbs) MAX
5. MOUNTING HOLE TORQUE:
0.9N-m (8 in-lbs) MAX.
6. INPUT WIRE SIZE: #4-6 AWG.
7. OUTPUT WIRE SIZE: #12-16 AWG.
8. ALL DIMENSIONS ARE REFERENCE.
9. HARDWARE BAGGED.

46377-20(OBSOLETE)Ⓔ	20	173.74 [6.84]	127.0 [5.00]	46376-20	47105-11
46377-18	18	157.99 [6.22]	111.00 [4.37]	46376-18	47105-11
46377-14(OBSOLETE)Ⓔ	14	126.24 [4.97]	79.25 [3.12]	46376-14	47105-11
46377-12	12	110.24 [4.34]	63.50 [2.50]	46376-12	47105-11
46377-10	10	95.25 [3.75]	47.62 [1.87]	46376-10	47105-11
46377-8	8	78.48 [3.09]	31.75 [1.25]	46376-8	47105-11
46377-6	6	62.74 [2.47]	15.85 [0.62]	46376-6	47105-11
PART NO.	POS.	A DIM.	B DIM.	ITEM 1	ITEM 2

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.															
		FIT/ FUNCTION CRITICAL CHARACTERISTICS													
<S>		SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL													
CPK		DENOTES CPK DIMENSIONS MINIMUM CPK VALUE													
		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS													
CP		DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE													
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF.ISO2768-M) FOR METAL, REF SPI PLASTICS															
DIMENSION MM		UP TO 0.5 - 3		OVER 3 - 6		UP TO 6 - 30		OVER 30 - 120		OVER 120 - 400		ANGLE			
TOLERANCES		±0.1		±0.1		±0.2		±0.3		±0.5		±0.5°			
NAME		DATE		 Littelfuse® Expertise Applied Answers Delivered											
DRAWN MJT		8/19/91													
CHECKED -		-													
-		-													
FORM NO: CVP-PE40-0003 REV A				TITLE FUSE BLOCK											
THIRD ANGLE PROJECTION															
				SIZE B		DWG. NO. 46377, CHART						REV. E			
DO NOT SCALE DRAWING				SCALE 1:2								SHEET 1 OF 1			