




REVISIONS				
REV.	DESCRIPTION	DATE	DESIGNED	APPROVED
A	FIRST ISSUE OF OUTLINE DRAWING	15-June-20	Gasparini	Tinto




Scale 1:2



Markinh showing:
-Code IVECO
-Code LITTELFUSE
-Manufacturing date according to LITTELFUSE standard

-Code IVECO
-LITTELFUSE production progressive code

Connector DIN 72585-A1-7 ways



PRESCRIPTIONS:

- Torque of screw M10= 19Nm max
- Fix the device with M6 screws and with torque of 6 ± 2 Nm
- Nuts and bolts supplied on the kit LITTELFUSE code 10844041

CHARACTERISTICS:

- Nominal working tension: 11 - 28.5 V
- Nominal working current: 10A
- Nominal working current main contacts: 500 A (1h at 23°C)
- Nominal max current main contact: 2000A for 5 sec
- External emergency switch - LITTELFUSE code 00227000

SAP drawing number:

Material and treatments:

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.						
linear dimensions						
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3
angle (for range of lengths)						
up to 10	>10 50	>50 120	>120 400	>400 1000	>1000 2000	>2000 5000
±1°30'	±1°	±0°30'	±0°15'	±0°15'	±0°15'	±0°15'
●	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL					
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL					
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE					
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS					
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE					
		NAME	DATE	 Expertise Applied Answers Delivered		
DRAWN	L. Dal Molin	07/05/2019				
CHECKED	-	-	-			
				TITLE		
				Electrical BDS		
FORM NO. CVP-PE40-0013 REV A		FIRST ANGLE PROJECTION				
		SIZE: A2	DWG. NO. OL-08075161	OUTLINE REV. A		
DO NOT SCALE DRAWING		SCALE 1:1			SHEET 1 OF 1	