






THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO #5300103. INITIAL RELEASE. DSILVA.	10/4/2022	L.ARGIL









STANDARD NOTES FOR MOLDED PARTS:

- MATERIAL: THERMOPLASTIC, COLOR BLACK.
- THE 3D MODEL OF THIS PART IS TO BE USED AS A REFERENCE ONLY.



SCALE 1:1

NO.		COMPONENT NO.		COMPONENT NAME				QTY/M		U/M	
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)											
.5 to 3		>3 to 6		>6 to 30		>30 to 120		>120 to 400		ANGLE	
±0.10		±0.10		±0.20		±0.30		±0.50		NONE	
DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.											
PER CHNPD20-008 PROCEDURE				FIT/ FUNCTION CRITICAL CHARACTERISTICS							
				SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL							
				DENOTES CPK DIMENSIONS MINIMUM CPK VALUE							
				DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS							
				DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE							
DRAWN		NAME		DATE		<div><b>Littelfuse</b> Expertise Applied   Answers Delivered</div> <div>TITLE BASE HWB18</div>					
CHECKED		DSILVA		7/19/2022							
		-		-							
		-		-							
		-		-							
FORM NO. CVP-PE40-0005 REV B						SIZE C DWG. NO. OUTLINE OL-868-965 REV. A					
THIRD ANGLE PROJECTION											
											
DO NOT SCALE DRAWING						SCALE 2:1			SHEET 1 OF 1		