




THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

- PDM NOTES:
1. MATERIAL: THERMOPLASTIC, UL94 V-0
 2. OPERATING TEMPERATURE RANGE: -40 °C TO +85 °C
 3. MATE WITH TYCO AMP MCP 2.8 FEMALE TERMINAL, FLR CABLE FOLLOW ISO 6722 CLASS C AND DIN 72511, DETAIL SEE CHART BELOW
 4. SIX (6) TERMINAL PORTS ARE CAPABLE OF HOLDING THREE (3) MINI FUSES OR A COMBINATION OF MIMI FUSES, MCASE, AND MINI CIRCUIT BREAKERS
 5. 2.8MM BLADES RATED FOR MAXIMUM 40A (AT 20°C AMBIENT TEMPERATURE),TOTAL MAXIMUM CURRENT 120A
 6. TPAS AND METAL BRACKET(868-964) TO BE PACKED ALONG WITH THE HOLDER SEPARATELY IN BULK, AND THE BASE WITH COVER,YELLOW LATCH, AND SEAL INSTALLED
 7. OPTIONAL TETHER (890009470) TO BE INSTALLED WITH THE PIN ON COVER AND THE PIN ON THE BASE
 8. OPTIONAL BRACKET (868-964) CAN BE SOLD SEPARATELY
 9. CAPABLE OF 25A CONTINUOUS CURRENT
 10. MOUNTING TORQUE: 5.5-6.5NM, USING M6 BOLT& LOCK WASHER
 11. INGRESS PROTECTION RATING: IP67
 12. IN EACH SINGLE CIRCUIT OF THIS HOLDER, THE MAX CONTINUOUS CURRENT WHICH CAN CARRY IS 30A.



OPTIONAL:
MCASE ADAPTER (875-584) WILL NEED
IF USING MCASE FUSE IN 2.8MM TERMINAL

NOTE:DESIGN AND APPLICATION FOR TE AMP MCP 2.8 FEMALE TERMINAL,DETAILS AS BELOW
WIRE SPEC: DIN 72551 AND ISO 6722, CLASS B

Wire Size range(mm2)	Insulation Diameter(mm) FLR	Material and Finish	Part Number Strip Form	TE Cable Seal Part Number	Cable Seal Color
0.35-0.50	1.2-1.4	1-xxx-1/1-xxx-3	968882	828904-1	Blue
0.5-1.0	1.4-2.1	1-xxx-1/1-xxx-2/1-xxx-3	968855	828904-2	
1.0-2.5	2.2-3.0	1-xxx-1/1-xxx-3	968857	828905-1	White
			Cable Seal Plug	828922-1	Natural

Material and Finish: 1-xxx-1 = CuNiSi, pre-tin plated
: 1-xxx-2 = CuNiSi, selective gold plated
: 1-xxx-3 = CuNiSi, selective silver plated

REVISIONS

ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PER EC # 515567: INITIAL RELEASE	3/30/2016	D.CHENG
	B	ECA# 516382 CHANGE DIMENSION 64.31+/-0.2 TO 64.31REF	9/21/2016	D.CHENG
	C	ECA# 518749 ADD PDM32005ZXM INTO TABLE DRAWING	05/Feb/2018	D.CHENG
	D	ECA# 520270 ADD THE MAX CONTINUOUS CURRENT IN NOTES	09/Jan/2019	D.CHENG

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.

● DENOTES PRODUCTS CRITICAL CHARACTERISTICS



CPK DENOTES CPK DIMENSIONS MINIMUM CPK VALUE

ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS

CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF.ISO2768-M)

DIMENSION	UP TO 0.5 - 3	OVER 3 - 6	UP TO 6 - 30	OVER 30 - 120	UP TO 120 - 400	OVER 400 - 1000	ANGLE
TOLERANCES	±0.1	±0.1	±0.2	±0.3	±0.5	±0.5°	


NAME	DATE	 Excerpt Applied Answer's Be. record No.6 Xinghai Street,Suzhou Industry Park,China Phone +86 512 6761 3189 Fax +86 512 6761 1489	
DRAWN	D.CHENG		
CHECKED	-	TITLE HWB6 ASSY MARKET	
	-		
	-	THIRD ANGLE PROJECTION 	
	-		
DO NOT SCALE DRAWING	SIZE C	DWG. NO. OL-PDM32000ZXM	REV. D

SCALE 1:1

SHEET 1 OF 3

THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PER EC # 515567: INITIAL RELEASE	3/30/2016	D.CHENG
	B	ECA# 516382 CHANGE DIMENSION 64.31+/-0.2 TO 64.31REF	9/21/2016	D.CHENG
	C	ECA# 518749 ADD PDM32005ZXM INTO TABLE DRAWING	05/Feb/2018	D.CHENG
	D	ECA# 520270 ADD THE MAX CONTINUOUS CURRENT IN NOTES	09/Jan/2019	D.CHENG




OPTIONAL:
MCASE ADAPTER (875-584) WILL NEED
IF USING MCASE FUSE IN 2.8MM TERMINAL


9	MCASE FUSE	1
8	MCASE ADAPTER	1
NO.	COMPONENT NAME	QTY

MARKET VERSION

HWB6 P/N	COVER TALLER CLEAR	COVER TALLER BLAC	BRACKET	COVER SHORT LF LOGO(BLK)
PDM32001ZXM	X			
PDM32002ZXM		X		
PDM32003ZXM	X		X	
PDM32004ZXM		X	X	
PDM32005ZXM				X

7	BRACKET NEW	1
6	TETHER HOLDER	1
5	TPA	1
4	BASE	1
3	YELLOW LATCH WITH GRIP	2
2	SILICON RUBBER	1
1	COVER	1
NO.	COMPONENT NAME	QTY

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.									
		DENOTES PRODUCTS CRITICAL CHARACTERISTICS							
CPK		DENOTES CPK DIMENSIONS MINIMUM CPK VALUE							
		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS							
CP		DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE							
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF.ISO2768-M)									
DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120	120 - 400	ANGLE			
TOLERANCES	±0.1	±0.1	±0.2	±0.3	±0.5	±0.5°			
NAME		DATE		 Exempted Applied Ansine's Be'ncord No.6 Xinghai Street,Suzhou Industry Park,China Phone +86 512 6761 3189 Fax +86 512 6761 1489					
DRAWN		D.CHENG 2/18/2016							
CHECKED		-							
-		-							
-		-		TITLE HWB6 ASSY MARKET					
-		-							
-		-							
THIRD ANGLE PROJECTION									
-									
-									
DO NOT SCALE DRAWING				SIZE C	DWG. NO.	OL-PDM320000ZXM			REV. D
				SCALE 1:1			SHEET 2 OF 3		



STEP1:OPEN THE YELLOW LATCHES BY HAND OR A SIMPLE TOOL LIKE SCREW DRIVER,
AND REMOVE COVER,

STEP2: PUT CABLE THROUGH THE CABLE SEAL AND STRIP THE CABLE AND CRIIMP THE CABLE AND CABLE SEAL WITH TYCO 2.8MM TERMINAL.





STEP3: BEND THE CABLE TO 2 LINES AND MAKE THE TPA GO THROUGH SMOOTHLY AND THEN PUSH THE CABLE AND TERMINAL TO BASE CABLE CAVITIES UNTIL HEAR A CLICK SOUND, THEN SNAPPING TPA TO BASE,

STEP4: INSERT 3 MINI FUSES OR COMBINATION OF MINI FUSE, MCASE FUSE(NEED ADAPTER), AND MINI CIRCUIT BREAKER,

STEP5: ASSEMBLE THE COVER (SEAL SEATED BY LATCHES) WITH BASE AND SNAPPING THE YELLOW LATCH,

STEP6: OPTIONAL: ASSEMBLE THE BRACKET TO BASE.

STEP7: OPTIONAL: ASSEMBLE THE TETHER TO PIN OF BASE AND COVER.

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.																													
	DENOTES PRODUCTS CRITICAL CHARACTERISTICS																												
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE																												
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS																												
CP	DENOTES CP DIMENSIONS. MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE																												
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO2768-M)																													
DIMENSION	0.5 - 3	UP TO 0.5	OVER 3 - 6	UP TO 0.5	OVER 6 - 30	UP TO 0.5	OVER 30 - 120	UP TO 0.5	OVER 120 - 400	UP TO 0.5	ANGLE																		
TOLERANCES	±0.1		±0.1		±0.2		±0.3		±0.5		±0.5°																		
<table><tr><td>DRAWN</td><td>NAME</td><td>DATE</td></tr><tr><td>CHECKED</td><td>D.CHENG</td><td>2/18/2016</td></tr><tr><td></td><td>-</td><td>-</td></tr><tr><td></td><td>-</td><td>-</td></tr><tr><td></td><td>-</td><td>-</td></tr><tr><td></td><td>-</td><td>-</td></tr></table>			DRAWN	NAME	DATE	CHECKED	D.CHENG	2/18/2016		-	-		-	-		-	-		-	-	<div><p>Extrinsic Applied ABBAS's Bay Road No.6 Xinjiahe Street, Suzhou Industry Park, China Phone +86 512 6761 3189 Fax +86 512 6761 1489</p></div>								
DRAWN	NAME	DATE																											
CHECKED	D.CHENG	2/18/2016																											
	-	-																											
	-	-																											
	-	-																											
	-	-																											
THIRD ANGLE PROJECTION			TITLE		HWB6 ASSY MARKET																								
			SIZE C	DWG. NO.	OL-PDM32000ZXM					REV. D																			
DO NOT SCALE DRAWING			SCALE 1:1						SHEET 3 OF 3																				