

VERSIONS AND PART NUMBERS							
CURREN RATE [A]	M5 2 HOLES	M5 2 HOLES	M5 1 HOLE	M5 2 HOLES CLEAR COVER	M6 1 HOLE	M6 2 HOLES	M5 2 HOLES
30	0498030.M	0498030.H	0498030.MX1M5	0498030.MXT	0498030.MX1M6	0498030.MXM6	0498030.MXTM6
40	0498040.M	0498040.H	0498040.MX1M5	0498040.MXT	0498040.MX1M6	0498040.MXM6	0498040.MXTM6
50	0498050.M	0498050.H	0498050.MX1M5	0498050.MXT	0498050.MX1M6	0498050.MXM6	0498050.MXTM6
60	0498060.M	0498060.H	0498060.MX1M5	0498060.MXT	0498060.MX1M6	0498060.MXM6	0498060.MXTM6
70	0498070.M	0498070.H	0498070.MX1M5	0498070.MXT	0498070.MX1M6	0498070.MXM6	0498070.MXTM6
80	0498080.M	0498080.H	0498080.MX1M5	0498080.MXT	0498080.MX1M6	0498080.MXM6	0498080.MXTM6
100	0498100.M	0498100.H	0498100.MX1M5	0498100.MXT	0498100.MX1M6	0498100.MXM6	0498100.MXTM6
125	0498125.M	0498125.H	0498125.MX1M5	0498125.MXT	0498125.MX1M6	0498125.MXM6	0498125.MXTM6
150	0498150.M	0498150.H	0498150.MX1M5	0498150.MXT	0498150.MX1M6	0498150.MXM6	0498150.MXTM6
175	0498175.M	0498175.H	0498175.MX1M5	0498175.MXT	0498175.MX1M6	0498175.MXM6	0498175.MXTM6
200	0498200.M	0498200.H	0498200.MX1M5	0498200.MXT	0498200.MX1M6	0498200.MXM6	0498200.MXTM6

MIDI 2 HOLES M5/M6 VERSIONS

MIDI 1 HOLE M5 VERSIONS

MIDI 1 HOLE M6 VERSIONS

CLEAR TOP HOUSING

OPAQUE HOUSING

ISOMETRIC VIEW

MIDI 32V						
TERMINAL MATERIAL:		COPPER				
TERMINAL PLATING:		TIN				
HOUSING MATERIAL: (BLACK)		PA66-GF25 (U.L. 94 FLAMMABILITY RATING - V0)				
CLEAR HOUSING MATERIAL:		PA6/66 (U.L. 94 FLAMMABILITY RATING - HB)				
LINEAR DIMENSIONS					ANGLES	RADI I
DIM	.5 - 6	6 - 30	30 - 120	120 - 400	±0.5°	±0.2
TOL	±0.1	±0.2	±0.3	±0.5		

3RD ANGLE
PROJECTION

CHICAGO, USA 773-628-1000

REVISION	DRWG. NO.
A	WEB-0498000.M