






REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO5300241:INITIAL RELEASE	15/APR/2023	Du.C



- NOTES:
- ASSOCIATED 3D CAD FILE DEFINES ALL NON-DIMENSIONED FEATURES.
 - MATERIAL: TPV BLACK
DUROMETER: 70~80 SHORE
FLAMMABILITY: UL94-V0
 - LF P/N: FHZ515

LIMIT DIMENSIONS OF RUBBER MOLDED PARTS FOR NOMINAL SIZE RANGES PER ISO IN LITTELFUSE									
CVP-NPD20-0002, DIMENSIONS mm									
0 to 4	>4 to 6	>6 to 10	>10 to 16	>16 to 25	>25 to 40	>40 to 63	>63 to 100	>100 to 160	>160 to 250
±0.10	±0.15	±0.20	±0.20	±0.25	±0.35	±0.40	±0.50	±0.70	±0.5%
									±0.5%
									NONE
DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.									
●	FIT/ FUNCTION CRITICAL CHARACTERISTICS								
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL								
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE								
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS								
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE								
DRAWN		NAME	DATE	 Expertise Applied Answers Delivered					
CHECKED		Rex.L	15/FEB/2022						
		Du.C	15/FEB/2022						
FORM NO: CVP-PE40-0005 REV B				TITLE					
THIRD ANGLE PROJECTION				5P ZCASE COVER					
		SIZE	DWG. NO.	REV.					
		C	OUTLINE	OL-FHZ515		A			
DO NOT SCALE DRAWING				SCALE 1:1			SHEET 1 OF 1		