







THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.



| REVISIONS |      |                                      |            |          |
|-----------|------|--------------------------------------|------------|----------|
| ZONE      | REV. | DESCRIPTION                          | DATE       | APPROVED |
|           | A    | INITIAL RELEASE. GCF 500000021764    | 12/17/2019 | DGK      |
| C4, D3    | B    | UPDATED LABEL AND NOTE 7. ECR 522500 | 7/29/2020  | DGK      |

- NOTES: UNLESS OTHERWISE SPECIFIED
- CONTACT ARRANGEMENT: SPST-NO
  - CONTINUOUS CURRENT RATING: 100 AMPS
  - CONTACT VOLTAGE RATING: 12 - 750 VDC
  - CONTACT TERMINALS NON-POLARIZED
  - HARDWARE: NONE
  - WEIGHT: 190 GRAMS (6.7 OZ.)
  - CERTIFICATIONS:  
UL RECOGNIZED FOR CANADA AND THE UNITED STATES  
EUROPEAN ECONOMIC AREA RECOGNIZED.  
RoHS COMPLIANT

| INTERPRET DRAWING TO ANSI/ASME Y14.5-1994.                                                                                                                                                      |                                                                                                                                                                      |                             |                                                                                                                                                          |           |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|
|                                                                                                            | FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL                                                                                                                        |                             |                                                                                                                                                          |           |
| <S>                                                                                                                                                                                             | SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL                                                                                                                   |                             |                                                                                                                                                          |           |
| CPK                                                                                                                                                                                             | DENOTES CPK DIMENSIONS MINIMUM CPK VALUE                                                                                                                             |                             |                                                                                                                                                          |           |
|                                                                                                            | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS |                             |                                                                                                                                                          |           |
| CP                                                                                                                                                                                              | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE            |                             |                                                                                                                                                          |           |
| DIMENSION; MM TOLERANCES UNLESS OTHERWISE SPECIFIED<br>ONE PLACE DECIMAL ± 0.5                      THREE PLACES DECIMAL ± 0.100<br>TWO PLACES DECIMAL ± 0.20                      ANGULAR ± 2° |                                                                                                                                                                      |                             |                                                                                                                                                          |           |
|                                                                                                                                                                                                 | NAME                                                                                                                                                                 | DATE                        |  <b>Littelfuse®</b><br><b>Expertise Applied   Answers Delivered</b> |           |
| DRAWN                                                                                                                                                                                           | DGK                                                                                                                                                                  | 11/20/2019                  |                                                                                                                                                          |           |
| CHECKED                                                                                                                                                                                         | AH                                                                                                                                                                   | 12/13/2019                  |                                                                                                                                                          |           |
|                                                                                                                                                                                                 | -                                                                                                                                                                    | -                           |                                                                                                                                                          |           |
|                                                                                                                                                                                                 | -                                                                                                                                                                    | -                           | <b>TITLE</b><br>DC CONTACTOR, 100 AMP<br>48 VDC, NON-POLAR TERMINALS                                                                                     |           |
|                                                                                                                                                                                                 | -                                                                                                                                                                    | -                           |                                                                                                                                                          |           |
| FORM NO: CVP-PE40-0004 REV A                                                                                                                                                                    |                                                                                                                                                                      |                             |                                                                                                                                                          |           |
| THIRD ANGLE PROJECTION                                                                                                                                                                          |                                                                                                                                                                      |                             |                                                                                                                                                          |           |
|                                                                                                            | SIZE<br>B                                                                                                                                                            | DWG. NO.<br>OL-DCNLEV100-EN | OUTLINE<br>B                                                                                                                                             | REV.<br>B |
| DO NOT SCALE DRAWING                                                                                                                                                                            |                                                                                                                                                                      |                             | SCALE 1:1                                                                                                                                                |           |
|                                                                                                                                                                                                 |                                                                                                                                                                      |                             | SHEET 1 OF 1                                                                                                                                             |           |

| ENGINEERING DESIGN DATA |                       |                       |                        |                    |                 |                      |                    |                        |
|-------------------------|-----------------------|-----------------------|------------------------|--------------------|-----------------|----------------------|--------------------|------------------------|
| COIL DATA               |                       |                       |                        |                    |                 | SHORT CIRCUIT        | DIELECTRIC VOLTAGE | ELECTRICAL LIFE        |
| COIL VOLTAGE (VDC)      | NOMINAL POWER (WATTS) | PICK-UP VOLTAGE (VDC) | DROP-OUT VOLTAGE (VDC) | MAX. VOLTAGE (VDC) | HOLDING CURRENT | MAX, 1/2 CYCLE, 60Hz | (VRMS)             | 100A @ 450VDC (CYCLES) |
| 48                      | 6.0                   | 33                    | 4.8                    | 52                 | 122mA           | 1250 A               | 2,200              | 10,000                 |