



THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	J	ECO #03189 NOTES	05/30/03	
	K	DIMENSIONS & VIEW	12/23/03	
	L	ECO # 12085 ADDED BLACK	03/16/12	
	M	ECO #521068 UPDATE DIMENSION C.MILLER	07/22/19	E.FERNANDEZ



- NOTES:
1. ALL STEEL PARTS PLATED
 2. ALL DIMENSIONS ARE REFERENCE ONLY
 3. MOUNTING THREADS 1"-11 1/2 NPSM-
MOUNTING TORQUE 10.8-13.5 Nm
(8-10 FT LBS) NOT TO EXCEED
13.5 Nm (10 FT LBS)
 4. STUD 3/8"-16 TIGHTENING TORQUE
8.1-10.8 Nm (6-8 FT LBS)
 5. ALL HARDWARE SUPPLIED IN BAG

6	88706	WASHER	1
5	83084	STUD 3/8"-16	1
4	84000	HEX NUT 3/8"-16	2
3	85049	LOCKWASHER 3/8"	2
2	83320	NUT LOCK 1-11 1/2	1
1	87394	INSULATOR, BLACK	1
ITEM	PART NO.	COMPONENT NAME	QTY

INTERPRET DRAWING TO ANSI/ASME Y14.5-1994.				
	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL			
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL			
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE			
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
DIMENSION; MM TOLERANCES UNLESS OTHERWISE SPECIFIED ONE PLACE DECIMAL ± 0.5 THREE PLACES DECIMAL ± 0.100 TWO PLACES DECIMAL ± 0.20 ANGULAR ± 2°				
DRAWN		NAME	DATE	 Littelfuse® Expertise Applied Answers Delivered
CHECKED		A.HOANG	7/25/19	
		-	-	
		-	-	
FORM NO: CVP-PE40-0004 REV A				TITLE FEED THRU STUD
THIRD ANGLE PROJECTION				
				
DO NOT SCALE DRAWING				
SIZE B		DWG. NO. 46211-01		REV. M
SCALE 1:1			SHEET 1 OF 1	