




THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO #5300103. INITIAL RELEASE. DSILVA	10/4/2022	L.ARGIL



NOTES:
1. MATERIAL: COPPER, TIN PLATED.

NO.	COMPONENT NO.	COMPONENT NAME	QTY	U	
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)					
.5 to 3	>3 to 6	>6 to 30	>30 to 120	>120 to 400	ANGLE
±0.05	±0.05	±0.10	±0.15	±0.20	NONE
DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.					
PER CHI-NPDP20-0008 PROCEDURE		FIT/ FUNCTION CRITICAL CHARACTERISTICS			
	<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL			
	CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE			
		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
	CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
	NAME	DATE	 Expertise Applied Answers Delivered TITLE STEPPED BUS BAR - FLEC TO FLEXMEGA		
DRAWN	DSILVA	7/27/2022			
CHECKED	-	-			
	-	-			
FORM NO: CVP-PE40-0003 REV B			TITLE STEPPED BUS BAR - FLEC TO FLEXMEGA		
THIRD ANGLE PROJECTION					
	SIZE	DWG. NO.	TITLE STEPPED BUS BAR - FLEC TO FLEXMEGA		
	B	OUTLINE			
DO NOT SCALE DRAWING			SCALE 2:1		SHEET 1 OF 1